

EMT Adapters and Clamps

Applications



- Adaptors are used to connect non-threaded fittings to threaded fittings.
- Clamps and straps are used to secure oval/round cables or support runs of rigid metal conduit, IMC and EMT.

Material

- Steel or malleable iron

Features

- Malleable iron clamps are exceptional rugged and strong.
- Steel clamps and adapters offer economy and have integral formed gussets for excellent strength.

Catalog Number	Trade Size (Inches)	Dimensions in Inches/Millimeters			Weight Lbs./Kgs. Per 100		
		A	B	C			
No-Thread to Threaded Fittings – Conversion Adapters – Steel							
	TWAD-50	1/2	0.44/ 11.2	0.13/ 3.3	1.00/ 25.4	2.20/ 1.00	
	TWAD-75	3/4	0.50/ 12.7	0.13/ 3.3	1.44/ 36.6	4.00/ 1.81	
	TWAD-100	1	0.63/ 16.0	0.13/ 3.3	1.50/ 38.1	6.00/ 2.72	
	TWAD-125	1-1/4	0.75/ 19.1	0.19/ 4.8	2.00/ 50.8	11.00/ 4.99	
	TWAD-150	1-1/2	0.75/ 19.1	0.19/ 4.8	2.25/ 57.2	12.00/ 5.44	
	TWAD-200	2	0.75/ 19.1	0.25/ 6.4	2.81/ 71.4	19.00/ 8.62	
Clamps – EMT – Malleable							
	TWCL-50MN	1/2	1.06/ 26.9	0.88/ 22.4	0.63/ 16.0	0.25/ 6.4	5.00/ 2.27
	TWCL-75MN	3/4	1.19/ 30.2	1.06/ 26.9	0.75/ 19.1	0.25/ 6.4	6.00/ 2.72
	TWCL-100MN	1	1.38/ 35.1	1.38/ 35.1	0.81/ 20.6	0.25/ 6.4	10.00/ 4.54
	TWCL-125MN	1-1/4	1.63/ 41.4	1.75/ 44.5	0.88/ 22.4	0.38/ 9.7	13.00/ 5.90
	TWCL-150MN	1-1/2	1.81/ 46.0	1.94/ 49.3	0.94/ 23.9	0.38/ 9.7	15.00/ 6.80
	TWCL-200MN	2	2.31/ 58.7	2.50/ 63.5	1.06/ 26.9	0.50/ 12.7	20.00/ 9.07

