

Fluorescent Hand Lamps

Explosionproof. 13 Watt Twin Tube and 26 Watt Quad

Class I, Division 1, Groups C, D
Class II, Division 1, Groups F, G

Features

- This portable, fluorescent light features durable, heavy-duty construction with non-metallic guard, swivel hook and handle assembly.
- The handle holds a 125 Volt rated ballast designed to operate on 50 or 60 Hz with recyclable thermal protection.
- "T" Number: T6.
- Easy maintenance.
- Completely watertight.
- No exposed metal parts.
- 900 lumens for 13 Watt unit.
- 1800 lumens for 26 Watt unit.
- Corrosion-resistant.
- 4"/101.6 mm outside diameter.
- 23-1/2"/596.9 mm length.
- 3-1/2 lbs/1.6 kgs.

Standard Materials

- Globe: tempered glass

Certifications and Compliances

- UL Listed: E43473
- UL Standard: 844



5227-0006

	Catalog Number
13 Watt Twin Tube Selection Chart	
Hand lamp with 50'/15.2 m 16/3-SO cord (male plug not included)	5227-0003
Twin tube hand lamp with out cord	5227-0006
26 Watt Quad Tube Selection Chart	
Hand lamp with 50'/15.2m 16/3-SO cord (male plug not included)	5227-0007
Quad tube hand lamp with out cord	5227-0008