

Areamaster™ 250/400 Integrally Ballasted Floodlights

70 W, 100 W, 150 W, 250 W, 400 W HPS; 175 W, 200 W, 250 W, 320 W, 400 W PSMH

NEC: For general, marine and hazardous locations
Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nR, Groups IIA, IIB, IIC
IP66

Marine type electric fixtures, outside type
(salt water)

Lamp	Line Voltage	For Class 1, Division 2 Classified Duty and Marine Yoke Mount	For General Duty		Class I, Zone 2 Yoke Mounting
		Catalog Number ②③	Yoke Mount Catalog Number ②	Slip-Fit Mount Catalog Number ①②	Catalog Number ③
High Pressure Sodium					
70 W HPS ④	120/208/240/277	G-AML271L-MT-I/2	—	—	G-AML271L-MT-Z2
	220 V 50 Hz	G-AML271L-225-I/2 ⑤	—	—	G-AML271L-225-Z2 ⑤
	480	G-AML271L-48-I/2	—	—	G-AML271L-48-Z2
100 W HPS ④	120/208/240/277	G-AML371L-MT-I/2	—	—	G-AML371L-MT-Z2
	220 V 50 Hz	G-AML371L-225-I/2 ⑤	—	—	G-AML371L-225-Z2 ⑤
	480	G-AML371L-48-I/2	—	—	G-AML371L-48-Z2
150 W HPS ④	120/208/240/277	G-AML471L-MT-I/2	—	—	G-AML471L-MT-Z2
	220 V 50 Hz	G-AML471L-225-I/2 ⑤	—	—	G-AML471L-225-Z2 ⑤
	480	G-AML471L-48-I/2	—	—	G-AML471L-48-Z2
250 W HPS	120/208/240/277	G-AM671L-MT-I/2	G-AM671L-MT	G-AM675L-MT	G-AM671L-MT-Z2
	230 V 50 Hz	G-AM671L-235-I/2 ⑥	G-AM671L-235 ⑥	G-AM675L-235 ⑥	G-AM671L-235-Z2 ⑥
	480	G-AM671L-48-I/2	G-AM671L-48	G-AM675L-48	G-AM671L-48-Z2
400 W HPS	120/208/240/277	G-AM771L-MT-I/2	G-AM771L-MT	G-AM775L-MT	G-AM771L-MT-Z2
	230 V 50 Hz	G-AM771L-235-I/2 ⑥	G-AM771L-235 ⑥	G-AM775L-235 ⑥	G-AM771L-235-Z2 ⑥
	480	G-AM771L-48-I/2	G-AM771L-48	G-AM775L-48	G-AM771L-48-Z2
Pulse Start Metal Halide					
175 W PSMH	120/208/240/277	G-AM571P-MT-I/2	G-AM571P-MT	G-AM575P-MT	G-AM571P-MT-Z2
	480	G-AM571P-48-I/2	G-AM571P-48	G-AM575P-48	G-AM571P-48-Z2
200 W PSMH	120/208/240/277	G-AM2071P-MT-I/2	G-AM2071P-MT	G-AM2075P-MT	G-AM2071P-MT-Z2
	480	G-AM2071P-48-I/2	G-AM2071P-48	G-AM2075P-48	G-AM2071P-48-Z2
250 W PSMH	120/208/240/277	G-AM671P-MT-I/2	G-AM671P-MT	G-AM675P-MT	G-AM671P-MT-Z2
	230 V 50 Hz	G-AM671P-235-I/2 ⑥	G-AM671P-235 ⑥	G-AM675P-235 ⑥	G-AM671P-235-Z2 ⑥
	480	G-AM671P-48-I/2	G-AM671P-48	G-AM675P-48	G-AM671P-48-Z2
320 W PSMH	120/208/240/277	G-AM3271P-MT-I/2	G-AM3271P-MT	G-AM3275P-MT	G-AM3271P-MT-Z2
	230 V 50 Hz	G-AM3271P-235-I/2 ⑥	G-AM3271P-235 ⑥	G-AM3275P-235 ⑥	G-AM3271P-235-Z2 ⑥
	480	G-AM3271P-48-I/2	G-AM3271P-48	G-AM3275P-48	G-AM3271P-48-Z2
400 W PSMH	120/208/240/277	G-AM771P-MT-I/2	G-AM771P-MT	G-AM775P-MT	G-AM771P-MT-Z2
	230 V 50 Hz	G-AM771P-235-I/2 ⑥	G-AM771P-235 ⑥	G-AM775P-235 ⑥	G-AM771P-235-Z2 ⑥
	480	G-AM771P-48-I/2	G-AM771P-48	G-AM775P-48	G-AM771P-48-Z2

① Slip-fits 2" or 2-1/2" pipe-size tenons.

② Add suffix -E to catalog number if provision for quartz emergency option is desired. Furnished with socket installed and pre-wired.

③ Quartz emergency option NOT available for Class I, Division 2 or Class I, Zone 2 fixtures. Classified duty floodlights have 1/2" N.P.T tapped hub for power entry. Use 221 °F/105 °C supply wire.

④ For Hot Restrike Option, add suffix -R.

⑤ For 120 V 50 Hz change -225 to -125, or for 240 V 50 Hz change -225 to -245.

⑥ For 120 V 50 Hz change -235 to -125.