

WSR and WSRD Interlocked Receptacle

With Enclosed Disconnect Switch

600 Vac, 250 Vdc, 30, 60, 100 Amp, 50/60 Hz, Fused and Non-fused for use with Powertite® ACP and CPH plugs.

NEMA 3, 3R, 4, 4X, 12

Plugs and Receptacles

PLUGS AND RECEPTACLES: ORDINARY LOCATION

| Amp | Wire Size AWG | Fusing † | HP at 600 Vac Std/Max 3-Phase | Without Viewing Window | With Viewing Window | Aux. Contacts ‡ 1 or 2 NO/NC | | Mating Plug |
|--|------------------|-----------|-------------------------------------|---------------------------|------------------------|---------------------------------|----------|-------------|
| Cast Aluminum Enclosure — NEMA 3, 3R, 4, 4X, 12 * | | | | | | | | |
| 30 | #14 to #2 | Fused | 7.5/20 | WSR3352 | N/A | WSAUX1 | WSAUX2 | ACP3034BC |
| | | Non-Fused | 30 | WSR33542 | N/A | WSAUX1 | WSAUX2 | ACP3034BC |
| 60 | #6 to #2 | Fused | 15/50 | WSR6352 | N/A | WSAUX1 | WSAUX2 | ACP6034BC |
| | | Non-Fused | 60 | WSR63542 | N/A | WSAUX1 | WSAUX2 | ACP6034BC |
| 100 | #4 to #1/0 | Fused | 30/75 | WSR10352 | N/A | WSAUX1 | WSAUX2 | ACP1034CD |
| | | Non-Fused | 75 | WSR103542 | N/A | WSAUX1 | WSAUX2 | ACP1034CD |
| Sheet Metal Enclosure — NEMA 3R, 12 * | | | | | | | | |
| 30 | #14 to #2 | Fused | 7.5/20 | WSRD3352SQ | WSRD3352WSQ | WSAUX1 | WSAUX2 | ACP3034BC |
| | | Non-Fused | 30 | WSRD33542SQ | WSRD33542WSQ | WSAUX1 | WSAUX2 | ACP3034BC |
| 60 | #6 to #2 | Fused | 15/50 | WSRD6352 ♦ | N/A | WSRDAUX1 | WSRDAUX2 | ACP6034BC |
| | | Non-Fused | 60 | WSRD63542 ♦ | N/A | WSRDAUX1 | WSRDAUX2 | ACP6034BC |
| | | Fused | 15/50 | WSRD6352SQ | WSRD6352WSQ | WSAUX1 | WSAUX2 | ACP6034BC |
| | | Non-Fused | 60 | WSRD63542SQ | WSRD63542WSQ | WSAUX1 | WSAUX2 | ACP6034BC |
| 100 | #4 to #1/0 | Fused | 30/75 | WSRD10352SQ | WSRD10352WSQ | WSAUX1 | WSAUX2 | ACP1034CD |
| | | Non-Fused | 75 | WSRD103542SQ | WSRD103542WSQ | WSAUX1 | WSAUX2 | ACP1034CD |
| Stainless Steel Enclosure — NEMA 3, 3R, 4, 4X, 12 * | | | | | | | | |
| 30 | #14 to #2 | Fused | 7.5/20 | WSRD3352N4SD | WSRD3352N4WSD | WSAUX1 | WSAUX2 | ACP3034BC |
| | | Non-Fused | 20 | WSRD33542N4SD | WSRD33542N4WSD | WSAUX1 | WSAUX2 | ACP3034BC |
| 60 | #6 to #2 | Fused | 15/50 | WSRD6352N4SD | WSRD6352N4WSD | WSAUX1 | WSAUX2 | ACP6034BC |
| | | Non-Fused | 50 | WSRD63542N4SD | WSRD63542N4WSD | WSAUX1 | WSAUX2 | ACP6034BC |
| 100 | #4 to #1/0 | Fused | 30/75 | WSRD10352N4SD | WSRD10352N4WSD | WSAUX1 | WSAUX2 | ACP1034CD |
| | | Non-Fused | 75 | WSRD103542N4SD | WSRD103542N4WSD | WSAUX1 | WSAUX2 | ACP1034CD |

Square D Auxiliary Contacts for WSR/WSRD Disconnect Switch †

| Interlock Type | 50 or 60 Hz Vac | Make | Break | Cont. | Vdc | Make and Break | Cont. | Catalog Number |
|-----------------------|-----------------|------|-------|-------|-----|----------------|-------|----------------|
| 1 NO/1 NC CONTACT | 120 | 40A | 15A | 15A | 115 | 0.50A | 15A | WSAUX1 |
| | 240 | 20A | 10A | 15A | 230 | 0.25A | 15A | |
| | 480 | 10A | 6A | 15A | — | — | — | |
| | 600 | 8A | 5A | 15A | 600 | 0.05A | 15A | |
| 2 NO/2 NC CONTACTS | 120 | 30A | 3.0A | 10A | 115 | 1.0A | 10A | WSAUX2 |
| | 240 | 15A | 1.5A | 10A | 230 | 0.30A | 10A | |
| | 480 | 7.5A | .75A | 10A | — | — | — | |
| | 600 | 6.0A | .60A | 10A | 600 | 0.10A | 10A | |

† Fuses not included in fused products. Class R fusing standard on WSRD fusible units and J Type on WSR. Product can be retrofitted with Class J, K, or S fusing.

‡ To order with auxiliary contacts installed, add suffix from this column to end of Catalog Number.

■ Standard Square D F-Series Disconnect Switch, except where noted.

♦ Cutler Hammer Disconnect Switch. Cutler Hammer auxiliary switch is 1 NO/1 NC or 2 NO/2 NC.

† Single pole single throw interlock kits are rated 1/2 HP @ 110 and 220 Vac. WSAUX1 utilizes a 9007A01 limit switch. WSAUX2 utilizes a 9007C03 limit switch.