








CPS 20 Factory Sealed Amp Pin and Sleeve Replacement Receptacles and CPP Plugs

Explosionproof

120-240 Vac, 20 Amp at 1 HP; 20 Amp at 24 Vdc. Dead-Front Safety Construction.

Class I, Division 1 and 2 Groups B+, C, D
Class II, Division 1 and 2 Groups F, G
NEMA 3RX*, 7BCD

*Does not intermate with
Contender® CPS 20 Amp
Pin and Sleeve Receptacles*

	Type	Number of Gangs	Wire/Pole	Hub Size (Inches)	Catalog Number
CPS Receptacle 15° Angle Type					
	Dead-End	—	2W, 3P	1/2	CPSA-2350
				3/4	CPSA-2375
CPS Receptacles with EFD Mounting Boxes					
	Dead-End	Single	2W, 3P	1/2	CPE1-2350
				3/4	CPE1-2375
				1	CPE1-23100
	Feed-Thru	Single	2W, 3P	1/2	CPC1-2350
				3/4	CPC1-2375
				1	CPC1-23100
	Dead-End	Two	2W, 3P	1/2	CPE2-2350
				3/4	CPE2-2375
				1	CPE2-23100
	Feed-Thru	Two	2W, 3P	1/2	CPC2-2350
				1	CPC2-23100
				3/4	CPC2-2375
CPS Replacement Receptacle and Cover Assembly					
	CPSR		2W, 3P		CPSR-23
	Replacement Spring Cover				CPSCA
CPR Replacement Receptacle Cover Assembly Only					
	CPR		2W, 3P		CPR-23
	Spring Cover Kit				CPRCA
	NEMA 3X Corrosion Resistance Kit •				CPS233RXKIT
Description			Wire/Pole	Cable Dia. (Inches)	Catalog Number
CPP Plugs for use with CPS Receptacles					
	Pressure Terminals				
	Plug amperes match receptacle ratings		2W, 3P	.536 to .639	CPP-2023

• NEMA 3X with Screw Cover Kit installed and cover full engaged.

† Suitable for Class 1, Group C, D, Class I Div 2 Group B, C, D, Class II, Groups F, G

◆ Shaded area indicates items suitable for Class I, Group B in addition to Class I, Groups C and D.