

Watertight Hubs

Zinc Die Cast, Insulated and Gasketed

Suitable for use in Class I, Division 2

Zinc Diecast Hubs — Insulated						
Catalog Number	Trade Size (Inches)	Dimensions in Inches/Millimeters		Dimensions in Inches/Millimeters		
		Hole Diameter Min. — Max.	Panel Thickness Min. — Max.	A	B	C
HUB-50DN †	1/2	0.86 — 0.91/ 21.8 — 23.1	0.03 — 0.25/ 0.8 — 6.4	0.84/21.3	0.64/16.3	1.44/36.6
HUB-75DN †	3/4	1.08 — 1.14/ 27.4 — 28.9	0.03 — 0.25/ 0.8 — 6.4	0.94/23.9	0.64/16.3	1.69/42.9
HUB-100DN †	1	1.33 — 1.41/ 33.8 — 35.8	0.03 — 0.25/ 0.8 — 6.4	1.03/26.2	0.78/19.8	2.00/50.8
HUB-125DN †	1-1/4	1.67 — 1.77/ 42.4 — 44.9	0.03 — 0.25/ 0.8 — 6.4	1.12/28.4	0.78/19.8	2.38/60.5
HUB-150DN †	1-1/2	1.92 — 2.02/ 48.8 — 51.3	0.06 — 0.25/ 1.5 — 6.4	1.12/28.4	0.78/19.8	2.75/69.9
HUB-200DN †	2	2.36 — 2.50/ 59.9 — 63.5	0.06 — 0.25/ 1.5 — 6.4	1.12/28.4	0.78/19.8	3.25/82.6
HUB-250DN †	2-1/2	2.86 — 3.00/ 72.6 — 76.2	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	3.72/94.5
HUB-300DN †	3	3.48 — 3.63/ 88.4 — 92.2	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	4.38/111.3
HUB-350DN †	3-1/2	3.98 — 4.16/ 101.1 — 105.7	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	4.94/125.5
HUB-400DN †	4	4.48 — 4.67/ 113.8 — 118.6	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	5.47/138.9

Grounding Style Hubs — Insulated								
Catalog Number	Trade Size (Inches)	Dimensions in Inches/Millimeters		Dimensions in Inches/Millimeters				
		Hole Diameter Min. — Max.	Panel Thickness Min. — Max.	D	E	F	G	H
HUBG-50DN	1/2	0.86 — 0.91/ 21.8 — 23.1	0.03 — 0.25/ 0.8 — 6.4	0.84/21.3	0.64/16.3	1.44/36.6	10—32x1/4	0.69/17.5
HUBG-75DN	3/4	1.08 — 1.14/ 27.4 — 28.9	0.03 — 0.25/ 0.8 — 6.4	0.94/23.9	0.64/16.3	1.69/42.9	10—32x1/4	0.78/19.8
HUBG-100DN	1	1.33 — 1.41/ 33.8 — 35.8	0.03 — 0.25/ 0.8 — 6.4	1.03/26.2	0.78/19.8	2.00/50.8	10—32x1/4	0.78/19.8
HUBG-125DN	1-1/4	1.67 — 1.77/ 42.4 — 44.9	0.03 — 0.25/ 0.8 — 6.4	1.12/28.4	0.78/19.8	2.38/60.5	1/4—20x3/8	0.81/20.6
HUBG-150DN	1-1/2	1.92 — 2.02/ 48.8 — 51.3	0.06 — 0.25/ 1.5 — 6.4	1.12/28.4	0.78/19.8	2.75/69.9	1/4—20x3/8	1.00/25.4
HUBG-200DN	2	2.36 — 2.50/ 59.9 — 63.5	0.06 — 0.25/ 1.5 — 6.4	1.12/28.4	0.78/19.8	3.25/82.6	1/4—20x1/2	1.00/25.4
HUBG-250DN	2-1/2	2.86 — 3.00/ 72.6 — 76.2	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	3.72/94.5	1/4—20x1/2	1.25/31.8
HUBG-300DN	3	3.48 — 3.63/ 88.4 — 92.2	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	4.38/111.3	1/4—20x1/2	1.25/31.8
HUBG-350DN	3-1/2	3.98 — 4.16/ 101.1 — 105.7	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	4.94/125.5	1/4—20x1/2	1.31/33.3
HUBG-400DN	4	4.48 — 4.67/ 113.8 — 118.6	0.06 — 0.31/ 1.5 — 7.9	1.56/39.6	1.06/26.9	5.47/138.9	1/4—20x1/2	1.31/33.3

† PVC coating available on select hubs. Add suffix **-PVC** to catalog number.

COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS

Commercial Products