

FM7™ Form-IN-Place Covers with Integral Gaskets

For FM7™ Unilet® Conduit Outlet Bodies.

Class I, Division 2
NEMA 3R

Applications

- Cover with integral gasket for FM7 conduit bodies.
- Can be used as replacement covers for installed bodies or in new installations.

Features

- Benefit from superior sealing, reduced inventory parts and faster installation times.
- Captive pan-head screws.
- Wedge-Lok™ clips (FM7 only) provide superior screwdriver torque and cover seating.
- High-strength, corrosion and weather resistant.
- Approved for wet locations.
- Fits all body configurations and sizes from 1/2" thru 4".

Standard Materials

- Stamped steel
- Stamped aluminum
- Cast grayloy-iron
- Cast aluminum





Certifications and Compliances

- UL Listed: E2527
- CSA Certified: 65183, Class 4413-02



Fittings

FITTINGS: CONDUIT BODIES

| Hub Size (Inches) | Stamped Steel | Stamped Aluminum | Cast Grayloy-Iron | Cast Aluminum |
|-------------------|---|---|---|---|
| |  |  |  |  |
| 1/2 | APP170IG | APP170IGSA | APP170FIG | APP170FIGSA |
| 3/4 | APP270IG | APP270IGSA | APP270FIG | APP270FIGSA |
| 1 | APP370IG | APP370IGSA | APP370FIG | APP370FIGSA |
| 1-1/4 | APP470IG | APP470IGSA | APP470FIG | APP470FIGSA |
| 1-1/2 | APP570IG | APP570IGSA | APP570FIG | APP570FIGSA |
| 2 | APP670IG | APP670IGSA | APP670FIG | APP670FIGSA |
| 2-1/2 & 3 | APP870IG | APP870IGSA | APP870FIG | APP870FIGSA |
| 3-1/2 & 4 | APP970IG | APP970IGSA | APP970FIG | APP970FIGSA |