





# FM8® Grayloy™ –Iron Unilet® Covers, Gaskets and Wiring Capacity

For use with Rigid Steel and IMC Conduit.

## Appleton FM8® Blank Covers and Gaskets \*

Body Size (inches)	Stamped Cover Steel	Cast Cover Grayloy–Iron †	Solid Gasket Neoprene	Open Gasket Neoprene
				
1/2	180	180F	GASK851N	—
3/4	280	280F	GASK852N	—
1	380	380F	GASK853N	—
1-1/4	480	480F	GASK854N	—
1-1/2	580	580F	—	GASK805N
2	680	680F	—	GASK806N
2-1/2	880	880F	—	GASK808N
3	880	880F	—	GASK808N
3-1/2	980	980F	—	GASK809N
4	980	980F	—	GASK809N

## Wiring Capacity: Combine Body and Cover Capacities for Total Usable Capacity per NEC 314.16(A)

Hub Size (inches)	Capacity (in <sup>3</sup> /dm <sup>3</sup> )						Stamped Cover	Cast Cover
	C	LB	LL, LR	T	TB	X		
1/2	5.00/ 0.08	5.00/ 0.08	5.00/ 0.08	6.00/ 0.10	6.00/ 0.10	6.00/ 0.10	0.50/ 0.01	0.30/ 0.00
3/4	8.00/ 0.13	8.00/ 0.13	8.00/ 0.13	10.00/ 0.16	10.00/ 0.16	10.00/ 0.16	0.80/ 0.01	0.80/ 0.01
1	13.00/ 0.21	13.00/ 0.21	13.00/ 0.21	15.50/ 0.25	15.50/ 0.25	15.50/ 0.25	1.00/ 0.02	1.00/ 0.02
1-1/4	24.00/ 0.39	24.00/ 0.39	24.00/ 0.39	25.00/ 0.41	25.00/ 0.41	25.00/ 0.41	1.50/ 0.02	1.50/ 0.02
1-1/2	42.50/ 0.70	42.50/ 0.70	42.50/ 0.70	44.00/ 0.72	44.00/ 0.72	44.00/ 0.72	1.80/ 0.03	7.50/ 0.12
2	105.00/ 1.72	105.00/ 1.72	105.00/ 1.72	105.00/ 1.72	105.00/ 1.72	105.00/ 1.72	4.50/ 0.07	12.50/ 0.20
2-1/2	200.00/ 3.28	200.00/ 3.28	200.00/ 3.28	200.00/ 3.28	—	—	12.30/ 0.20	34.50/ 0.57
3	217.00/ 3.56	217.00/ 3.56	217.00/ 3.56	217.00/ 3.56	—	—	12.30/ 0.20	34.50/ 0.57
3-1/2	—	380.00/ 6.23	—	—	—	—	24.00/ 0.39	65.30/ 1.07
4	—	400.00/ 6.55	—	—	—	—	24.00/ 0.39	65.30/ 1.07

\* Covers furnished with stainless steel screws, 1-1/2" – 4" covers provided with 4 screws  
 † PVC coating available on select FM8 covers. Add suffix -PVC to catalog number.