








# FM8® Grayloy™ –Iron Unilet® Conduit Bodies

For use with Rigid Steel and IMC Conduit.

FITTINGS: CONDUIT BODIES

## Appleton FM8® Conduit Bodies ‡

Hub Size (Inches)	C	LB	LL	LR
				
1/2	<b>C18</b>	<b>LB18</b>	<b>LL18</b>	<b>LR18</b>
3/4	<b>C28</b>	<b>LB28</b>	<b>LL28</b>	<b>LR28</b>
1	<b>C38</b>	<b>LB38</b>	<b>LL38</b>	<b>LR38</b>
1-1/4	<b>C448</b>	<b>LB448</b>	<b>LL448</b>	<b>LR448</b>
1-1/2	<b>C58</b>	<b>LB58</b>	<b>LL58</b>	<b>LR58</b>
2	<b>C68</b>	<b>LB68</b>	<b>LL68</b>	<b>LR68</b>
2-1/2	<b>C78</b>	<b>LB78</b>	<b>LL78</b>	<b>LR78</b>
3	<b>C88</b>	<b>LB888</b>	<b>LL888</b>	<b>LR888</b>
3-1/2	—	<b>LB98</b>	—	—
4	—	<b>LB108</b>	—	—
Hub Size (Inches)	T	TB	X	
				
1/2	<b>T18</b>	<b>TB18</b>	<b>X18</b>	
3/4	<b>T28</b>	<b>TB28</b>	<b>X28</b>	
1	<b>T38</b>	<b>TB38</b>	<b>X38</b>	
1-1/4	<b>T448</b>	<b>TB448</b>	<b>X448</b>	
1-1/2	<b>T58</b>	<b>TB58</b>	<b>X58</b>	
2	<b>T68</b>	<b>TB68</b>	<b>X68</b>	
2-1/2	<b>T78</b>	—	—	
3	<b>T88</b>	—	—	

‡ PVC coating available on all FM8 bodies. Add suffix **-PVC** to catalog number.