

Presented By: Candela Corporation

Contact Phone: 800-922-9226

Contact E-mail: sales@candelaCorp.com

Customer Name:

Project Name:

Fixture Type:



GE Lighting

66954 - LET75W12V

GELT75A27712RSL

Previous SKU: 901075277

GENERAL CHARACTERISTICS

Ambient Temp [Max]	50 °C
Ambient Temp [Min]	0 °C
Storage Temperature	min-(-10), max(70)°C
Line Voltage Regulation (+/-)	120-277
Product Technology	Halogen
CC/CVvalue	Voltage line depended
Output Power (W)	75 W
Output Current (A)	6.25 A
Output Voltage[Min]	11.2 V
Output Voltage[Max]	11.8 V
Output Voltage[Nom]	11.5 V
Output Voltage Range (dimming) (V)	0-11.8 V
Total Harmonic Distortion (THD)	15 %

PRODUCT INFORMATION

Product Code	66954
Description	GELT75A27712RSL
Alternative Unit Of Measure	CASE

DIMENSIONS

Nominal Length	63.0 mm
Width	33.0 mm
Height	20.0 mm
Weight	0.1 kg

Lead Color	Qty	Exit	Length (1 in.)
Black	1	Terminals	200mm
Blue	1	Terminals	250mm
White	1	Terminals	200mm

ELECTRICAL CHARACTERISTICS

Power Factor Correction	Passive
Power Factor %	0.95
Inrush Current Limiter	No
Output Current Frequency-Hertz	33 kHz
Supply Current Freq nominal Hz	50 Hz
60 Hz	Input Current Range [Max]
0.35 A	Input Current Range [Min]
0.35 A	Input Voltage Range [Min] (V)
252 V	Input Voltage Range [Max]
305 V	Dimming Capability