



PSR

SELF-REGULATING, PRE-TERMINATED CABLE

PSR is a parallel resistance, self-regulating cable that is provided in pre-terminated lengths with factory sealed connections. The cable is manufactured with a water-resistant TPE outer jacket. Cables are rated at 5 watts per foot at 50°F/10°C. 120 Vac models have an integral three-wire plug with pilot light; 240 Vac models have a three-wire pigtail. PSR cables are UL Listed to Canadian Safety Standards and CSA Certified for ordinary locations.



CATALOG NUMBER	DESCRIPTION	CTN QTY	CTN WGT	UPC	CERTIFICATIONS
PSR1006	6' length, 30 watts, 120 Vac	5	10	0-13627-06907-7	
PSR1012	12' length, 60 watts, 120 Vac	5	14	0-13627-06908-4	
PSR1018	18' length, 90 watts, 120 Vac	5	14	0-13627-06913-8	
PSR1024	24' length, 120 watts, 120 Vac	5	14	0-13627-06909-1	
PSR1050	50' length, 250 watts, 120 Vac	5	23	0-13627-06910-7	
PSR1075	75' length, 375 watts, 120 Vac	2	13	0-13627-06911-4	
PSR1100	100' length, 500 watts, 120 Vac	2	16	0-13627-06912-1	
PSR2006	6' length, 30 watts, 240 Vac	5	10	0-13627-06867-4	
PSR2012	12' length, 60 watts, 240 Vac	5	14	0-13627-06868-1	
PSR2018	18' length, 90 watts, 240 Vac	5	14	0-13627-06873-5	
PSR2024	24' length, 120 watts, 240 Vac	5	14	0-13627-06869-8	
PSR2050	50' length, 250 watts, 240 Vac	5	23	0-13627-06870-4	
PSR2075	75' length, 375 watts, 240 Vac	2	13	0-13627-06871-1	
PSR2100	100' length, 500 watts, 240 Vac	2	16	0-13627-06872-8	