

ETP Steel EMT Set Screw Connectors

4000S Series Connectors

Application

- To ground and secure EMT raceways to boxes and enclosures.

Features

- Heavy steel walls.
- Concretetight when taped.
- Pre-set/pre-staked set screws.
- Male hub threads — NPS.
- Available with insulated throat.
- Three-way combination screws 1/2" thru 1".
- Slotted hexhead screw 1-1/4" thru 4".
- Insulated throat connector rated 90 °C.

Material/Finish

- Steel/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14895, E14815
- CSA Standard: C22.2 No. 18.3
- cUL Listed: E14895
- CSA Certified: 028507
- NEMA: FB-1



4050S — 4100S



4125S — 4400S

Trade Size (Inches)	Catalog Number	Insulated Throat Catalog Number	Dimensions in Inches/Millimeters			Weight Lbs./Kgs. Per 100
			Body Length	Maximum Diameter	Thread Length	
1/2	4050S	4050ST	1.03/26.2	0.84/21.3	0.44/11.2	10.00/4.54
3/4	4075S	4075ST	1.09/27.7	1.08/27.4	0.44/11.2	15.00/6.80
1	4100S	4100ST	1.19/30.2	1.31/33.3	0.44/11.2	23.00/10.43
1-1/4	4125S	4125ST	1.75/44.5	1.69/42.9	0.56/14.2	42.00/19.05
1-1/2	4150S	4150ST	1.94/49.3	1.94/49.3	0.56/14.2	53.00/24.04
2	4200S	4200ST	2.19/55.6	2.38/60.5	0.63/16.0	75.00/34.02
2-1/2	4250S	4250ST	2.38/60.5	3.13/79.5	0.88/22.4	130.00/58.97
3	4300S	4300ST	2.88/73.2	3.75/95.3	0.88/22.4	230.00/104.33
3-1/2	4350S	4350ST	3.00/76.2	4.25/108.0	1.00/25.4	250.00/113.40
4	4400S	4400ST	3.19/81.0	4.75/120.7	1.00/25.4	250.00/113.40