



moving air in style.

Builder Unipack

CATALOG NUMBER: CF701
FINISHES: APPLIANCE WHITE, BRUSHED STEEL & OIL RUBBED BRONZE
STYLE: PRO SERIES COLLECTION
DIAMETER: 52" WITH 5 BLADES
MOTOR WARRANTY: LIMITED LIFETIME

MOTOR

- This motor offers consistent high quality and reliable performance for an economical price.
- 153 x 15 mm size, 14-pole motor offers the most efficient performance available.
- Permanently sealed stainless bearings for lasting performance and no lubricating.
- Quiet operation using superior triple capacitor for starting and controlling speed.
- Three forward and three reverse speeds.
- Quick connect plug allows easy servicing of speed control and reversing switch.

HOUSING

- High quality, carbon stamped steel fan housing, switch cup and ceiling canopy.
- Fan housing is a sleek 280 mm diameter with an attractive vent design.
- Triple electrical plating and painting give a deep, rich finish.
- Emerson inspectors ensure quality.
- Integrated light kit accepts two 60-watt candelabra bulbs (included)

BLADES

- 5 mm composite wood construction from the highest quality blade manufacturer.
- All blade sets are balanced to within one gram, thus ensuring wobble-free operation.
- Designed specifically for use with this motor to give optimum air movement.

HANGING SYSTEM

- Hanging ball and bracket are both made of die-cast zinc for durable wear. The industry uses a stamped steel bracket and plastic ball, which wears more quickly and does not control wobble.
- 42" wire leads accommodate up to a 3' downrod with no splicing required.
- Triple-locking unthreaded downrod system.

HIGH SPEED ENERGY INFORMATION

- Airflow - 4860 Cubic Feet Per Minute
- Electricity Use - 63 Watts (Excludes Lights)
- Airflow Efficiency - 77 Cubic Feet Per Minute Per Watt