



moving air in style.

Pro Series ES

CATALOG NUMBER: CF713
FINISHES: APPLIANCE WHITE, BRUSHED STEEL & OIL RUBBED BRONZE
STYLE: PRO SERIES COLLECTION
DIAMETER: 50"
MOTOR WARRANTY: LIMITED LIFETIME - ENERGY STAR APPROVED

MOTOR

- This motor offers consistent high quality and reliable performance for an economical price.
- 153 x 15 mm size, 14-pole motor offers the most efficient performance available.
- High quality shielded stainless bearings for lasting performance and no lubricating.
- Quiet operation using superior triple capacitor for starting and controlling speed.
- Three forward and three reverse speeds.
- Listed for damp locations.

HOUSING

- High quality, stamped steel switch cup and ceiling canopy.
- Fan housing is completely covered with a rust-resistant paint finish – inside and out.
- Finishes far exceed the industry norm in durability and beauty.
- A hard, transparent epoxy lacquer is added as a final coat for additional protection.
- All hardware is stainless steel to prevent rusting.
- All manufacturing steps undergo continuous quality inspections.
- Integrated light kit accepts three 13-watt medium base compact fluorescent bulbs (included).

BLADES

- 5mm composite wood construction from the highest quality blade manufacturer.
- All blades are balanced to within one gram, thus ensuring wobble-free operation.

HANGING SYSTEM

- Hanging ball and bracket are both made of die-cast zinc for durable wear. The industry uses a stamped steel bracket and plastic ball, which wears more quickly and does not control wobble.
- 42" wire leads accommodate up to a 3' downrod with no splicing required.
- Extra sage, triple-locking unthreaded downrod system.
- Snugger style application for low ceiling applications.

HIGH SPEED ENERGY INFORMATION

- Airflow - 5063 Cubic Feet Per Minute
- Electricity Use - 65 Watts (Excludes Lights)
- Airflow Efficiency - 78 Cubic Feet Per Minute Per Watt