

## Controls



SW605

Six Speed LED Wall Control

Six fan speeds with LED indicator

Full range light dimmer (250 Watts max) with independent uplight/downlight operation

1.0 amps fan load

One-touch reverse

White, Light Almond and Ivory switch cover plates included

Canopy mount receiver sold separately

For use with RC188, RC212 and RCK55 receivers