

Dry-Type/Cased Isolated General Purpose Three-Phase

3 - 15 kVA Indoor/Outdoor Type QMS 3 115°C Rise UL Listed C-UL Listed								GO-90E
Input Voltage	Output Voltage	KVA	Frequency (Hz)	Taps	Wiring Diagram No. ¹	Product Number	List Price	
480 Volts Delta	208 Y/120Volts	3	60 Hz	(2) 5% taps below rated primary volts.	8	9T21J3000	\$1344.00	
480 Volts Delta	208 Y/120Volts	3	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	9	9T21J3002	\$1344.00	
480 Volts Delta	208 Y/120Volts	6	60 Hz	(2) 5% taps below rated primary volts.	8	9T21J6000	\$1848.00	
480 Volts Delta	208 Y/120Volts	6	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	9	9T21J6002	\$1848.00	
480 Volts Delta	208 Y/120Volts	9	60 Hz	(2) 5% taps below rated primary volts.	21	9T21J9000	\$2100.00	
480 Volts Delta	208 Y/120Volts	9	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	22	9T21J9001	\$2226.00	
480 Volts Delta	480 Y/277 Volts	9	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	22	9T21J9710	\$2310.00	
480 Volts Delta	480 Y/277 Volts	15	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	22	9T21J1712	\$2730.00	
480 Volts Delta	208 Y/120Volts	15	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	22	9T21J1000	\$2940.00	
480 Volts Delta	208 Y/120Volts	15	60 Hz	(2) 5% taps below rated primary volts.	21	9T21J1702	\$2730.00	
480 Volts Delta	240 Volts Delta	3	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	11	9T21J3001	\$1344.00	
480 Volts Delta	240 Volts Delta	6	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	11	9T21J6001	\$1848.00	
480 Volts Delta	240 Volts Delta	9	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	10	9T21J9704	\$2310.00	
480 Volts Delta	240 Volts Delta	15	60 Hz	(4) 2 1/2% taps: 2 above and 2 below rated primary volts.	10	9T21J1701	\$2730.00	
600 Volts Delta	208 Y/120 Volts	3	60 Hz	(2) 5% taps below rated primary volts.	21	9T21J3708	\$1428.00	
600 Volts Delta	208 Y/120 Volts	6	60 Hz	(2) 5% taps below rated primary volts.	8	9T21J6016	\$1680.00	
600 Volts Delta	208 Y/120 Volts	9	60 Hz	(2) 5% taps below rated primary volts.	21	9T21J9705	\$2310.00	
600 Volts Delta	208 Y/120 Volts	15	60 Hz	(2) 5% taps below rated primary volts.	21	9T21J1703	\$2730.00	

15 - 1500 kVA Indoor Type QL UL Listed								GO-66A
Input Voltage	Output Voltage	KVA	Frequency (Hz)	Taps	Wiring Diagram No. ¹	Product Number ²	List Price	
480 Volts Delta	208 Y/120 Volts	15	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T23B3871	\$2793.00	
480 Volts Delta	208 Y/120 Volts	30	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T23B3872	\$3272.00	
480 Volts Delta	208 Y/120 Volts	45	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T23B3873	\$3935.00	
480 Volts Delta	208 Y/120 Volts	50	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T23B3864	\$4754.00	
480 Volts Delta	208 Y/120 Volts	75	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T23B3874	\$5920.00	
480 Volts Delta	208 Y/120 Volts	112.5	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T23B3875	\$7869.00	
480 Volts Delta	208 Y/120 Volts	150	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T23B3876	\$10261.00	
480 Volts Delta	208 Y/120 Volts	225	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T30G0007	\$13922.00	
480 Volts Delta	208 Y/120 Volts	300	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T30G0008	\$17587.00	
480 Volts Delta	208 Y/120 Volts	400	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T30G0089	\$24309.00	
480 Volts Delta	208 Y/120 Volts	500	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T30G0009	\$29107.00	
480 Volts Delta	208 Y/120 Volts	750	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T30G0010	\$51063.00	
480 Volts Delta	208 Y/120 Volts	1000	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	12	9T30G0011	\$58481.00	
480 Volts Delta	240 Volts Delta	15	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	13	9T23B3881	\$2913.00	
480 Volts Delta	240 Volts Delta	30	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	13	9T23B3882	\$3272.00	
480 Volts Delta	240 Volts Delta	45	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	13	9T23B3883	\$3935.00	
480 Volts Delta	240 Volts Delta	75	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	13	9T23B3884	\$5920.00	
480 Volts Delta	240 Volts Delta	112.5	60 Hz	(6) 2 1/2% taps: 2 above and 4 below rated primary volts.	13	9T23B3885	\$7869.00	

¹See page 8-17 for wiring diagrams.

²For Outdoor NEMA 3R Enclosure add suffix G62 to product number. Consult factory for 1500 kVA model.

Product Number Selection Instructions: See Page 8-2
Maximum Dimensions and Weights: See Page 8-16

distributed by AA Electric 1-800-237-8274 www.aaelectric.com

