

» S1K Series UPS

Economical and compact protection from damaging impulses due to power interruptions

Features

- Lightweight, compact design
- Four NEMA 5-15R outlets
- Step sine wave output
- Data-line surge protection for phone or network
- RS-232 DB9 communication interfaces
- Includes software and cable
- Input/output voltage — 115 VAC, 50/60 Hz
- Two-year warranty



SOLAHD

Mfr.'s Model No.	VA/Watts	Input/Output Connections	Typical Back-Up Time (Minutes for PC with 15" Monitor)	Approx. Ship Weight (lbs.)	Price
120 x 240V Primary; 24V Secondary; 60 Hz					
S1K320	320/240	5-15P/5-15R (3) Battery, (1) Surge	10	8.8 lbs.	\$183.96
S1K520	520/340	5-15P/5-15R (3) Battery, (1) Surge	15	11.6 lbs.	\$217.71
S1K650	650/390	5-15P/5-15R (3) Battery, (1) Surge	15	8.1 lbs.	\$364.50
S1K850	850/600	5-15P/5-15R (3) Battery, (1) Surge	25	10.8 lbs.	\$513.02
S1K1200	1200/720	5-15P/5-15R (3) Battery, (1) Surge	30	10.8 lbs.	\$817.57
S1K1500	1440/900	5-15P/5-15R (4) Battery	70	30 lbs.	\$899.50
Mfr.'s Model No.	Description				Price
Accessories					
S1K-PMBRK	Hardware for Wall/Panel Mount (not applicable to S1K1500 and S1K650)				\$40.50

» S3K Series Mini-Tower Line-Interactive UPS

Protects against severe power disturbances, including over/under voltages, through line-interactive technology

Features

- Line-interactive automatic voltage regulation (AVR) topology
- Data-line protection for telephone or networks
- Sine wave output
- Built-in surge protection
- User-replaceable, hot-swappable batteries
- Advanced microprocessor design improves reliability
- RS-232 communication port
- Fully digitized, microprocessor controlled
- UPSMON power management software
- 120 VAC, 50/60 Hz input/output
- Two-year warranty



Mfr.'s Model No.	VA/Watts	Input/Output Connections	Typical Back-Up Time (Minutes for PC with 15" Monitor)	Approx. Ship Weight	Price
S3K700	700/480	Detached 5-15P/(4) 5-15R	5/14	34.1 lbs.	\$869.12
S3K1000	1000/750	Detached 5-15P/(4) 5-15R	4/13	37 lbs.	\$1,206.62
S3K1600	1440/1200	Attached 5-15P/(6) 5-15R	3/10	70.4 lbs.	\$1,628.52

» S4K2UC and S4K2U-5C Industrial On-Line UPS

True on-line (double-conversion) protection eliminates a wider range of potential power problems

Features

- All-metal bezel — rugged industrial design
- Higher output power factor of 0.9
- Slim 2U tower design that is convertible to rack-mount standard, saves space
- Hardwire capability enables permanent installation
- PWM inverter reduces output voltage distortion
- Hot-swappable, user-replaceable battery
- Available external battery packs for extended backup times*
- Integral Dynamic Bypass mode to reduce shutdowns
- Automatic restart
- Automatic and manual battery test
- Integrally sealed, non-spillable batteries
- Intellislot port, USB port, and terminal communication block
- S4K2UC operates with 120 VAC, 50/60 Hz power
- S4K2U-5C provides flexible L-N output voltage
- Two-year warranty



Mfr.'s Model No.	VA/Watts	Input/Output Connections	Typical Back-Up Time at Full/Half Load (Minutes)	Weight	Price
S4K2UC					
S4K2U700-C	700/630	(1) 5-15P/(6) 5-15R	11/27	44.1 lbs.	\$1,573.60
S4K2U1000-C	1000/900	(1) 5-15P/(6) 5-15R	7/17	44.1 lbs.	\$1,999.56
S4K2U1500-C	1500/1350	(1) 5-15P/(6) 5-15R	4/11	57.3 lbs.	\$2,512.50
S4K2U2000-C	2000/1800	(1) 5-20P/(6) 5-20R (15/20A)	3/11	57.3 lbs.	\$3,158.58
S4K2U3000-C	3000/2700	(1) L5-30P/(6) 5-20R (15/20A), (1) L5-30R	3/11	79.4 lbs.	\$5,123.72
S4K2U-5C					
S4K2U1000-5C	1000/900	(1) IEC 320 C14/(6) IEC 320 C13	6/17	44.1 lbs.	\$2,197.30
S4K2U2000-5C	2000/1800	(1) IEC 320 C20/(6) IEC 320 C13	3/11	57.3 lbs.	\$3,322.10
S4K2U3000-5C	3000/2700	(1) IEC 320 C20/(6) IEC 320 C13, (1) IEC 320 C19	3/11	79.4 lbs.	\$5,279.46

*Contact your local Carlton-Bates representative for additional information on the available external battery packs.