

## DM Duplex Receptacle

### DESCRIPTIONS

Packaged in a touch-proof enclosure to eliminate the possibility of accidental shock. The universal mounting foot allows the outlet box to be mounted either vertically or horizontally in your panel. Touch-proof screw terminal block provides a reliable connection.

### FEATURES

- DIN-rail mount duplex receptacle
- Vertical or horizontal mounting
- Snap on foot provides fast installation or can be fixed with screws in control cabinet
- Fits on 35 mm wide DIN-rail
- Ground prong reversed for greater protection
- Screw terminal connection via touch-proof terminal blocks
- Available with GFI (Ground Fault Interrupting)
- UR Recognized

### APPLICATIONS

- Test & Diagnostic Equipment
- Computers/Printers
- Power Tools
- Soldering Iron
- Displays
- Lighting
- Fan



### GENERAL SPECIFICATIONS

#### Technical Data

Rated Voltage..... 120 V AC  
 Rated Current..... 15 AMPS  
 Maximum Wire Size ..... #10 AWG

#### Housing Data

Color ..... Black  
 Material..... PVC V01550  
 Maximum Temperature ..... 40°C

#### Dimensions

Length..... 5.32 in. (135 mm)  
 Width..... 2.95 in. (75 mm)  
 Depth ..... 2.56 in. (65 mm)

### DM Duplex Receptacle Selection Chart

AMP	CATALOG NUMBER	APPROX. SHIP WEIGHT LBS (Kg)
15	DRR15	.41 (.19)
15	DRR15GFI	.46 (.21)