

SELECTION CHARTS

GROUP A



120 X 240 PRIMARY VOLTS—24 SECONDARY VOLTS—50/60 Hz

CATALOG NO.	VA RATING	EUROPEAN* RATING	APPROX. DIMENSIONS INCHES (CM.)						APPROX. SHIP WEIGHT LBS. (Kg.)
			A	B	C	D	E	F	
FS150									
FS175									
FS1100									
FS1150									
FS1250									
FS1350									
FS1500									
FS1750									
FS11000	1000	870	4.76 (12.1)	6.75 (17.1)	6.03 (15.3)	5.75 (14.6)	2.86 (7.3)	.31 x .50 (0.8 x 1.3)	26 (11.8)

Reference Group IC (CE01):
CE Series Industrial Control Transformers
50-750 VA
See Pg 72

GROUP B

240 X 480, 230 X 460, 220 X 440 PRIMARY VOLTS—120/115/110 SECONDARY VOLTS—50/60 Hz

CATALOG NO.	VA RATING	EUROPEAN* RATING	APPROX. DIMENSIONS INCHES (CM.)						APPROX. SHIP WEIGHT LBS. (Kg.)
			A	B	C	D	E	F	
FS250									
FS275									
FS2100									
FS2150									
FS2250									
FS2300									
FS2350									
FS2500									
FS2750									
FS21000	1000	870	4.76 (12.1)	6.75 (17.1)	6.03 (15.3)	5.75 (14.6)	2.86 (7.3)	.31 x .50 (0.8 x 1.3)	26 (11.8)
FS21500	1500	1290	6.01 (15.3)	6.75 (17.1)	6.03 (15.3)	5.75 (14.6)	4.13 (10.5)	.31 x .50 (0.8 x 1.3)	38 (17.2)
FS22000	2000	1680	6.51 (16.5)	6.75 (17.1)	6.03 (15.3)	5.75 (14.6)	4.63 (11.8)	.31 x .50 (0.8 x 1.3)	44 (20.0)
FS23000	3000	2465	7.44 (18.9)	7.50 (19.1)	6.68 (17.0)	6.50 (16.5)	6.47 (16.4)	.41 x .81 (1.0 x 2.1)	60 (27.2)

Reference Group VIC (CE06):
CE Series Industrial Control Transformers
50-750 VA
See Pg 73

GROUP C

240/416/480/600; 230/400/460/575; 220/380/440/550; 208/500 PRIMARY VOLTS
99/120/130; 95/115/125; 91/110/120; 85/100/110 SECONDARY VOLTS—50/60 Hz

CATALOG NO.	VA RATING	EUROPEAN* RATING	APPROX. DIMENSIONS INCHES (CM.)						APPROX. SHIP WEIGHT LBS. (Kg.)
			A	B	C	D	E	F	
FS350	50	50	2.59 (6.6)	3.75 (9.5)	3.64 (9.2)	3.13 (8.0)	1.70 (4.3)	.22 x .50 (0.6 x 1.3)	5 (2.3)
FS3150	150	150	3.31 (8.4)	4.50 (11.4)	4.15 (10.5)	3.75 (9.5)	2.18 (5.5)	.22 x .50 (0.6 x 1.3)	8 (3.6)
FS3250	250	250	3.61 (9.2)	4.88 (12.4)	4.46 (11.3)	4.06 (10.3)	2.33 (5.9)	.22 x .50 (0.6 x 1.3)	11 (5.0)
FS3350	350	345	4.69 (11.9)	4.88 (12.4)	4.46 (11.3)	4.06 (10.3)	3.48 (8.8)	.22 x .50 (0.6 x 1.3)	17 (7.7)
FS3500	500	490	4.39 (11.2)	6.75 (17.1)	6.03 (15.3)	5.75 (14.6)	2.48 (6.3)	.31 x .50 (0.8 x 1.3)	22 (10.0)
FS3750	750	720	5.18 (13.2)	6.75 (17.1)	6.03 (15.3)	5.75 (14.6)	3.31 (8.4)	.31 x .50 (0.8 x 1.3)	30 (13.6)
FS31000	1000	870	6.18 (15.7)	6.75 (17.1)	6.03 (15.3)	5.75 (14.6)	4.30 (10.9)	.31 x .50 (0.8 x 1.3)	39 (17.7)
FS31500	1500	1290	6.26 (15.9)	7.50 (19.1)	6.68 (17.0)	6.50 (16.5)	5.26 (13.4)	.41 x .81 (1.0 x 2.1)	51 (23.1)
FS32000	2000	1680	7.76 (19.7)	7.50 (19.1)	7.70 (19.6)	6.50 (16.5)	6.75 (17.1)	.41 x .81 (1.0 x 2.1)	66 (29.9)
FS33000	3000	2465	8.88 (22.6)	11.92 (30.3)	8.83 (22.4)	6.75 (17.1)	5.75 (14.6)	.41 x .81 (1.0 x 2.1)	70 (31.8)