



Dependable Power for Any Application

Product Datasheet

240 Δ Primary Volts - 480Y/277 Secondary Volts - 3 \emptyset Dry Type Distribution Transformer - Three Phase

Catalog #: T3796931S



PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	15.00
Primary Voltage:	240Δ
Secondary Voltage:	480Y/277
Frequency:	60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	18.86 (48.0)
Width (In./cm):	20.30 (51.6)
Depth (In./cm):	9.03 (22.90)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Floor
Wiring Diagram:	70

PACKAGING

Ship Weight (Lbs/Kg):	245 (111.1)
-----------------------	-------------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf