



Actual

Catalog Number: 1HPW
Product ID: 7TAH006120R0001
UPC Number: 78378620036
Status: Active

Type HPW Plated Split-Bolt Connector with Spacer and Washer made of Copper Alloy for Use on Copper, Aluminum, ACSR Conductors. Conductor Range for Equal Main and Tap 1 Str.-8 Sol.

- Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Spacer and washer of tin plated electrolytic copper.
- Contoured spacer and bell mouth washer distribute pressure over large area of conductor. Large contoured spacer provides wide separation between copper and aluminum conductors.
- Splicing, tapping or terminating conductors in power and grounding electrical connection.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Split-Bolt
Special Features	Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Spacer and washer of tin plated electrolytic copper.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Copper Alloy
Finish	Electro Tin-Plated

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Outer Quantity	100
Outer Dimensions (inches)	7.4x6.5x5.7
Weight Uom	16.94 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com