



Actual

Catalog Number: 2B350X
Product ID: 7TAH006160R0014
UPC Number: 78378640011
Status: Active

Copper Type 2BX - One piece Two-Bolt Connector without spacer for Wire Range Main: 4/0 Str. - 350 kcmil Tap: 4 Sol. - 350 kcmil , Bolt Size 3/4

- Single-piece construction. Castings and bolts of high-strength copper alloy. Neoprene washer holds free bolt in place during installation.
- UL 486A listed for copper conductor only.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Two-Bolt Connector
Special Features	Single-piece construction. Castings and bolts of high-strength copper alloy. Neoprene washer holds free bolt in place during installation.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	4/0 Str. - 350 kcmil
Conductor Range (Tap/Secondary)	4 Sol. - 350 kcmil
Bolt Size	42798

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Quantity	1
Inner Dimensions (inches)	7.3x3.8x5.2
Outer Quantity	12
Outer Dimensions (inches)	19x10.7x8.7
Weight Uom	61.69 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com