



Actual

Catalog Number: 2B500PW
Product ID: 7TAH006160R0020
UPC Number: 78378640026
Status: Active

Aluminum Type 2BPW - Two-Bolt Connector with Spacer for Wire Range Main: 397.5-4 - 397.5-336.4 Tap: 500-4 Sol. - 500-350, Bolt Size 3/4

- Single-piece construction.
- UL 486A listed for copper conductor only.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Two-Bolt Connector
Special Features	Single-piece construction.
Standard	UL E9809
Material	Aluminum
Conductor Range (Main/Primary)	397.5-4 - 397.5-336.4
Conductor Range (Tap/Secondary)	500-4 Sol. - 500-350
Bolt Size	42798

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Aluminium

Packaging

Inner Quantity	1
Inner Dimensions (inches)	5x3.37x6.5
Outer Quantity	10
Outer Dimensions (inches)	10.1x5.2x3.7
Weight Uom	95.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com