



Actual

Catalog Number: BC24
Product ID: 7TAH007320R0003
UPC Number: 78378612454
Status: Active
Replacement Catalog: CC 24

C-Crimps Copper Compression Connector, Run: #2 Sol - #2 Str, Tap #8 Sol - #4 Str, Length 3/4 Inch, Height 63/64 Inch

- E-Z-Ground® connectors are designed for direct burial and offer a safe, efficient alternative to exothermic welding products.
- Application Tools: TBM14M, 13100A, TBM15I

North American Specifications (UNSPSC)

UNSPSC	39121428 Electrical taps
IGCC	4600 Electrical taps
Brand Name	Blackburn
Type	E-Z-Ground Compression Grounding
Special Features	E-Z-Ground® connectors are designed for direct burial and offer a safe, efficient alternative to exothermic welding products.
Standard	UL E9809
Conductor Size	#2 Sol. - #2 Str
Material	Copper

Packaging

Inner Quantity	100
Inner Dimensions (inches)	6x6x3.5
Outer Quantity	400
Outer Dimensions (inches)	13.187x7.75x7
Weight Uom	8.13 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com