



Actual

Catalog Number: CS72
Product ID: 7TAA267190R0011
UPC Number: 78378610060
Status: Active

Aluminum 2 Inch Service Entrance Compression Splice for Wire Range - End A: 2 6/1,7/1 ASCR, 1-2 Stranded, Red, End B: 4 6/1,7/1 ASCR, 3-4 Stranded, 2 Solid, Orange, Die: 5/8

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Service Entrance Splices
Special Features	Constructed from Aluminum for High Conductivity. Solid Center Barriers and large Chamfers for easy cable insertion. Prefilled with Oxide Inhibitor to prevent oxidation and keep out moisture. All Splices are color coded and marked with strip lengths, installation die codes and compression locations, providing easy identification for easy installation.
Application	Basic, uninsulated Splices for Service Entrances. For Combinations of Aluminum-to-Aluminum or Aluminum-to-Copper Conductors.
Standard	RUS Accepted. Complies with ANSI C119.4 when properly installed on Aluminum-to-Aluminum or Aluminum-to-Copper Conductors.
Size	2 Inch
Connection	Crimp/ Compression
Conductor Range	End A: 2 6/1,7/1 ASCR, 1-2 Stranded, End B: 4 6/1,7/1 ASCR, 3-4 Stranded, 2 Solid,
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Inner Quantity	100
Inner Dimensions (inches)	7.2x4.8x5.4
Outer Quantity	800
Outer Dimensions (inches)	20.1x11.6x8.4
Weight Uom	5.69 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com