



Representative

**Catalog Number:** CS77  
**Product ID:** 7TAA267190R0016  
**UPC Number:** 78378610107  
**Status:** Active

Aluminum 2 Inch Service Entrance Compression Splice for Wire Range - End A: 1/0 ASCR, 1/0 Stranded, Yellow, End B: 2 6/1,7/1 ASCR, 1-2 Stranded, Red, Die: 5/8

### North American Specifications (UNSPSC)

|                          |  |
|--------------------------|--|
| UNSPSC                   | 39121449 Wire or cable compression splice  |
| IGCC                     | 4669 Wire or cable compression splice  |
| Brand Name               | Blackburn  |
| Type                     | Service Entrance Splices   |
| Special Features         | Constructed from Aluminum for High Conductivity. Solid Center Barriers and large Chamfers for easy cable insertion. Prefilled with Oxide Inhibitor to prevent oxidation and keep out moisture. All Splices are color coded and marked with strip lengths, installation die codes and compression locations, providing easy identification for easy installation. |
| Application              | Basic, uninsulated Splices for Service Entrances. For Combinations of Aluminum-to-Aluminum or Aluminum-to-Copper Conductors.   |
| Standard                 | RUS Accepted. Complies with ANSI C119.4 when properly installed on Aluminum-to-Aluminum or Aluminum-to-Copper Conductors.  |
| Size                     | 2 Inch   |
| Connection               | Crimp/ Compression   |
| Conductor Range          | End A: 1/0 ASCR, 1/0 Stranded, End B: 2 6/1,7/1 ASCR, 1-2 Stranded   |
| Number Of Conductors     | 2  |
| Material                 | Aluminum   |
| Insulation               | None   |
| Mounting                 | None   |
| Environmental Conditions | All Seasons / Conditions   |

### Packaging

|                           |                   |
|---------------------------|-------------------|
| Inner Quantity            | 100               |
| Inner Dimensions (inches) | 6.8x5.3x4.69      |
| Outer Quantity            | 800               |
| Outer Dimensions (inches) | 20x11x7           |
| Weight Uom                | 4.75 lbs. per 100 |

### Documents / Support Tools

|                         |                      |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)