



Representative

**Catalog Number:** CTL1-2516  
**Product ID:** 7TAH007200R0061  
**UPC Number:** 78378613122  
**Status:** Active

Type CTL Copper Two-Hole Lug, Short Barrel, Max 35kV, Wire Size 1 Str or #2 Weld, 5/16 Inch Bolt Size, Tin Plated, Die Color Code Green

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Short Barrel Copper Lug
Special Features	Short Barrel Copper Lug
Standard	UL E9809
Stud Size	5/16 Inch
Number Of Holes	2
Voltage Rating	35KV
Material	Copper
Color	Green

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	3.5x3x2.5
Outer Quantity	250
Outer Dimensions (inches)	12.45x6.25x3.6
Weight Uom	5 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)