



Representative

Catalog Number: CTL2502
Product ID: 7TAH007200R0066
UPC Number: 78378613196
Status: Active

Type CTL Copper Two-Hole Lug, Short Barrel, Max 35kV, Wire Size 250 kcmil or 4/0 Weld, 1/2 Inch Bolt Size, Tin Plated, Die Color Code Yellow

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Short Barrel Copper Lug
Special Features	Short Barrel Copper Lug
Standard	UL E9809
Stud Size	1/2 Inch
Number Of Holes	2
Voltage Rating	35KV
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

Packaging

Inner Quantity	10
Inner Dimensions (inches)	5.5x4x3
Outer Quantity	100
Outer Dimensions (inches)	24x11.2x4.2
Weight Uom	21.81 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com