



Actual

Catalog Number: GTC24
Product ID: 7TAA014260R0007
UPC Number: 78378633313
Status: Active

Copper Tower Ground Clamp, 2-Piece, Wire Range 2/0 Str. - 250 kcmil

- Castings of high-strength, corrosion-resistant copper alloy. Bolt features square shank to prevent turning and enable clamp to be tightened with a single wrench.
- These two-piece clamps are designed for connecting ground lead cable to flat metal surface - ideal for grounding substations on tower footings.

North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Mechanical Grounding
Special Features	Castings of high-strength, corrosion-resistant copper alloy. Bolt features square shank to prevent turning and enable clamp to be tightened with a single wrench.
Conductor Size	2/0 Str. - 250 kcmil
Conductor Material	Copper
Insulation	Non-insulated
Length	1-15/16

Packaging

Inner Quantity	1
Inner Dimensions (inches)	5x3.37x6.5
Outer Quantity	25
Outer Dimensions (inches)	5x5x5
Weight Uom	40 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com