



Actual

Catalog Number: GUV3025
Product ID: 7TAA014500R0014
UPC Number: 78378680370
Status: Active

U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 2/0 - 250, Rod Size 3 to 3-1/2 Inches, IPS Pipe Size Max 3 Inches, Length 5-9/16 Inches, Width 4-13/16 Inches, Depth 1-9/16 Inches

- Excellent for connecting copper or copper-clad steel grounding conductor to ground rod or pipe. Specially designed spacer provides proper alignment between cable and electrode and affords more positive contact area.
- All components cast or forged from copper alloy.

North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Ground Clamps
Special Features	Excellent for connecting copper or copper-clad steel grounding conductor to ground rod or pipe. Specially designed spacer provides proper alignment between cable and electrode and affords more positive contact area.
Standard	UL E3060, CSA 12798
Conductor Size	#2/0 - 250 kcmil
Conductor Material	Copper
Insulation	No
Length	5-9/19 Inches

European Specifications (ETIM)

ETIM	EC000511 Tube earthing clamp for lightning protection
Material	Copper

Packaging

Inner Dimensions (inches)	5x3.37x6.5
Outer Quantity	10
Outer Dimensions (inches)	19.1x11x8
Weight Uom	1.76 lbs. Each

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com