



Actual

**Catalog Number:** JAB12H  
**Product ID:** 7TAA014200R0008  
**UPC Number:** 78378680072  
**Status:** Active

Ground Rod Clamps Type JAB , Rod Size 1/2, Wire Range 10 Sol - 2 Str, Hex Head Bolt

- Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.
- Both hex head bolts and socket set screws available.

### North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Ground Rod Clamps
Special Features	Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.
Standard	UL E3060
Conductor Material	Copper
Insulation	No

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	7.6x4.8x5.5
Outer Quantity	100
Outer Dimensions (inches)	7.6x5.45x4.7
Weight Uom	10 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000478

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)