



Representative

Catalog Number: KL22-1
Product ID: 7TAA267190R0032
UPC Number: 78378604750
Status: Active

Aluminum 3-1/2 Inch Service Entrance Compression Splice for Wire Range - End A: 4 Str., 4 Str. Compact, Orange, End B: 4 Str., 4 Str. Compact, Orange, Die: 840

North American Specifications (UNSPSC)

| | |
|--------------------------|--|
| UNSPSC | 39121449 Wire or cable compression splice |
| IGCC | 4669 Wire or cable compression splice |
| Brand Name | Blackburn |
| Type | Service Entrance Connectors |
| Special Features | Splices large conductors required for commercial service, use as low cost reducing sleeve. All sizes can be installed with popular mechanical and hydraulic tools. Center stop assures proper conductor positioning. Quick identifications with color-coded foil caps. |
| Application | For Combinations of Aluminum-to-Aluminum and Aluminum-to-Copper Conductors |
| Standard | Passes the requirements of ANSI C119.4 |
| Size | 3-1/2 Inch |
| Connection | Crimp/ Compression |
| Conductor Range | End A: 4 Stranded, 4 Stranded. Compact, End B: 4 Stranded, 4 Stranded. Compact |
| Number Of Conductors | 2 |
| Material | Aluminum |
| Insulation | None |
| Mounting | None |
| Environmental Conditions | All Seasons / Conditions |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 25 |
| Inner Dimensions (inches) | 6.75x5.25x3.7 |
| Outer Quantity | 250 |
| Outer Dimensions (inches) | 21x11.25x8 |
| Weight Uom | 19.56 lbs. per 100 |

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com