



Representative

Catalog Number: KL54-1
Product ID: 7TAA267190R0041
UPC Number: 78378605004
Status: Active

Aluminum 3-1/2 Inch Service Entrance Compression Splice for Wire Range - End A: 3/0 AS-CR, 4/0 Str. Compact, Orange, End B: 4 ASCR, 3-4 Str., 2 Sol., Orange, Die: 840

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Service Entrance Connectors
Special Features	Splices large conductors required for commercial service, use as low cost reducing sleeve. All sizes can be installed with popular mechanical and hydraulic tools. Center stop assures proper conductor positioning. Quick identifications with color-coded foil caps.
Application	For Combinations of Aluminum-to-Aluminum and Aluminum-to-Copper Conductors
Standard	Passes the requirements of ANSI C119.4
Size	3-1/2 Inch
Connection	Crimp/ Compression
Conductor Range	End A: 3/0 ASCR, 4/0 Stranded. Compact, End B: 4 ASCR, 3-4 Stranded, 2 Solid.
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6.75x5.25x3.7
Outer Quantity	250
Outer Dimensions (inches)	21x11.25x8
Weight Uom	17.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com