



Actual

**Catalog Number:** XT12  
**Product ID:** 7TAA267290R0001  
**UPC Number:** 78378640030  
**Status:** Active

Copper Type XT - Clamp for Tee-Tap, Cross, Parallel and End-to-End for Wire Range Main: 1 Stranded - 4/0 Stranded Tap: 6 Solid - 2 Stranded, Bolt Size 5/16

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Mechanical Connector
Special Features	Design allows for free wrench rotation which speeds installation.
Application	Multi-purpose Connector
Connection	Bolt
Number Of Conductors	2
Material	Casting of Copper Alloy, Bolts of Silicon Bronze
Finish	Bare
Enclosure	None
Voltage Rating	35kV
Insulation	None
Environmental Conditions	All Seasons / Conditions
Conductor Range (Main/Primary)	4/0 Stranded - 1 Stranded
Conductor Range (Tap/Secondary)	2 Stranded-6 Solid
Number of Conductors/Ports (Main/Primary)	1
Number of Conductors/Ports (Tap/Secondary)	1
Number Of Mounting Holes	zero
Bolt Size	5/16 inch

### Packaging

Inner Quantity	12
Inner Dimensions (inches)	7.3x3.7x5.2
Outer Quantity	120
Outer Dimensions (inches)	10.56x7.25x19.12
Weight Uom	43.75 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)