



Actual

Catalog Number: XT13
Product ID: 7TAA267290R0003
UPC Number: 78378640031
Status: Active

Copper Type XT - Clamp for Tee-Tap, Cross, Parallel and End-to-End for Wire Range Main: 1 Stranded - 4/0 Stranded Tap: 1 - 4/0 Stranded, Bolt Size 3/8

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Mechanical Connector
Special Features	Design allows for free wrench rotation which speeds installation.
Application	Multi-purpose Connector
Connection	Bolt
Number Of Conductors	2
Material	Casting of Copper Alloy, Bolts of Silicon Bronze
Finish	Bare
Enclosure	None
Voltage Rating	35kV
Insulation	None
Environmental Conditions	All Seasons / Conditions
Conductor Range (Main/Primary)	4/0 Stranded - 1 Stranded
Conductor Range (Tap/Secondary)	4/0 Stranded-1 Stranded
Number of Conductors/Ports (Main/Primary)	1
Number of Conductors/Ports (Tap/Secondary)	1
Number Of Mounting Holes	zero
Bolt Size	3/8 inch

Packaging

Inner Quantity	9
Inner Dimensions (inches)	5x3.37x6.5
Outer Quantity	90
Outer Dimensions (inches)	10.5x7.25x19
Weight Uom	66.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com