

SELECTION GUIDES

SINGLE PHASE

Catalog No.	Amp Rating	Voltage Range AC	Voltage Range DC	Frequency	Output Voltage	Mtbf (Life)	Efficiency	UL/CUL	CE
DR1-24013	1.3	94-264	-	50/60 Hz	24 VDC	> 17 years	89% typ.	YES	YES
DR1-24025	2.5	90-265	110-300	50/60 Hz	24 VDC (24-28 adj)	> 17 years	85% typ.	YES	YES
DR1-2405	5	90-265	90-300	50/60 Hz	24 VDC (24-28 adj)	> 17 years	88% typ.	YES	YES
DR1-2410	10	90-265	90-300	50/60 Hz	24 VDC (24-28 adj)	> 17 years	88% typ.	YES	YES
DR1-2420	20	90-265	90-300	50/60 Hz	24 VDC (24-28 adj)	> 17 years	88% typ.	YES	YES

THREE PHASE

Catalog No.	Amp Rating	Voltage Range AC	Voltage Range DC	Frequency	Output Voltage	Mtbf (Life)	Efficiency	UL/CUL	CE
DR3-2405	5	3x360-550	-	50/60 Hz	24 VDC (24-28 adj)	> 17 years	90% typ.	YES	YES
DR3-2410	10	3x360-550	-	50/60 Hz	24 VDC (24-28 adj)	> 17 years	90% typ.	YES	YES
DR3-2420	20	3x360-550	-	50/60 Hz	24 VDC (24-28 adj)	> 17 years	90% typ.	YES	YES
DR3-2440	40	3x360-550	-	50/60 Hz	24 VDC (24-28 adj)	> 17 years	91% typ.	YES	YES

SINGLE PHASE

Catalog No.	APPROX. DIMENSIONS INCHES (Cm)			WEIGHT LBS (Kg)
	H	D	W	
DR1-24013	2.99 (7.6)	2.91 (7.4)	1.50 (3.8)	0.33 (0.1)
DR1-24025	4.23 (10.7)	3.84 (9.7)	1.65 (4.2)	0.99 (0.4)
DR1-2405	4.53 (11.5)	5.94 (15.1)	2.13 (5.4)	1.65 (0.7)
DR1-2410	5.00 (12.7)	8.03 (20.4)	2.68 (6.8)	3.31 (1.5)
DR1-2420	8.23 (20.9)	9.17 (23.3)	3.31 (8.4)	5.95 (2.7)

THREE PHASE

Catalog No.	APPROX. DIMENSIONS INCHES (Cm)			WEIGHT LBS (Kg)
	H	D	W	
DR3-2405	5.00 (12.7)	7.01 (17.8)	2.68 (6.8)	2.87 (1.3)
DR3-2410	5.00 (12.7)	7.01 (17.8)	2.68 (6.8)	2.87 (1.3)
DR3-2420	8.23 (20.9)	8.94 (22.7)	3.31 (8.4)	5.07 (2.3)
DR3-2440	9.53 (24.2)	10.63 (27.0)	4.17 (10.6)	9.92 (4.5)

DR SERIES DIMENSIONAL DRAWINGS

