

Fast-acting 5x20 mm fuses

GDA

IEC 5x20 mm high-breaking capacity fast-acting ceramic tube fuses



| Amps | Catalog no.* |
|--------|--------------|
| 500 mA | GDA-500MA |
| 630 mA | GDA-630MA |
| 1 | GDA-1A |
| 1.25 | GDA-1.25A |
| 1.6 | GDA-1.6A |
| 2 | GDA-2A |
| 2.5 | GDA-2.5A |
| 3.15 | GDA-3.15A |
| 4 | GDA-4A |
| 5 | GDA-5A |
| 6.3 | GDA-6.3A |

* 5 Fuses per pack, 10 packs per shelf carton.

GDB

IEC 5x20 mm fast-acting glass tube fuses



| Amps | Catalog no.* |
|--------|--------------|
| 160 mA | GDB-160MA |
| 2 | GDB-2A |
| 4 | GDB-4A |
| 6.3 | GDB-6.3A |
| 8 | GDB-8A |
| 10 | GDB-10A |

* 5 Fuses per pack, 10 packs per shelf carton.

GMA

UL 5x20 mm fast-acting glass tube fuses

See page 48 for available assortments.



| Amps | Catalog no.* | Retail pack** |
|--------|--------------|---------------|
| 63 mA | GMA-63MA | — |
| 100 mA | GMA-100MA | — |
| 125 mA | GMA-125MA | — |
| 200 mA | GMA-200MA | BP/GMA-200MA |
| 250 mA | GMA-250MA | BP/GMA-250MA |
| 300 mA | GMA-300MA | — |
| 315 mA | GMA-315MA | — |
| 500 mA | GMA-500MA | BP/GMA-500MA |
| 600 mA | GMA-600MA | — |
| 750 mA | GMA-750MA | BP/GMA-750MA |
| 800 mA | GMA-800MA | — |
| 1 | GMA-1A | BP/GMA-1A |
| 1.25 | GMA-1.25A | — |
| 1.5 | GMA-1.5A | — |
| 1.6 | GMA-1.6A | — |
| 2 | GMA-2A | BP/GMA-2A |
| 2.5 | GMA-2.5A | — |
| 3 | GMA-3A | BP/GMA-3A |
| 3.15 | GMA-3.15A | — |
| 3.5 | GMA-3.5A | — |
| 4 | GMA-4A | — |
| 5 | GMA-5A | BP/GMA-5A |
| 6 | GMA-6A | BP/GMA-6A |
| 7 | GMA-7A | BP/GMA-7A |
| 8 | GMA-8A | — |
| 10 | GMA-10A | BP/GMA-10A |

* 5 Fuses per pack, 10 packs per shelf carton.
** 5 Fuses per pack, 5 packs per shelf carton.

Time-delay 5x20 mm fuses

GDC

IEC 5x20 mm time-delay glass tube fuses



| Amps | Catalog no.* | Retail pack** |
|--------|--------------|---------------|
| 500 mA | GDC-500MA | — |
| 1 | GDC-1A | — |
| 1.6 | GDC-1.6A | — |
| 2 | GDC-2A | — |
| 2.5 | GDC-2.5A | — |
| 3.15 | GDC-3.15A | — |
| 4 | GDC-4A | — |
| 5 | GDC-5A | BP/GDC-5A |
| 6.3 | GDC-6.3A | — |

* 5 Fuses per pack, 10 packs per shelf carton.
** 5 Fuses per pack, 5 packs per shelf carton.

GMC

UL 5x20 mm medium time-delay glass tube fuses



| Amps | Catalog no.* | Retail pack** |
|--------|--------------|---------------|
| 500 mA | GMC-500MA | BP/GMC-500MA |
| 630 mA | GMC-630MA | — |
| 1 | GMC-1A | — |
| 1.5 | GMC-1.5A | — |
| 1.6 | GMC-1.6A | — |
| 2 | GMC-2A | — |
| 3 | GMC-3A | — |
| 3.5 | GMC-3.5A | — |
| 4 | GMC-4A | — |
| 5 | GMC-5A | BP/GMC-5 |
| 6 | GMC-6A | — |
| 7 | GMC-7A | BP/GMC-7 |

* 5 Fuses per pack, 10 packs per shelf carton.
** 5 Fuses per pack, 5 packs per shelf carton.

GMD

UL 5x20 mm medium time-delay glass tube fuses



| Amps | Catalog no.* |
|--------|--------------|
| 500 mA | GMD-500 MA |
| 1 | GMD-1A |
| 2 | GMD-2A |
| 3 | GMD-3A |

* 5 Fuses per pack, 10 packs per shelf carton.

GMF

Non-rejection time-delay in-line fuse with cap



| Amps | Catalog no.* |
|--------|--------------|
| 2-1/2 | GMF-2-1/2 |
| 2-8/10 | GMF-2-8/10 |
| 3 | GMF-3 |
| 3-2/10 | GMF-3-2/10 |
| 4 | GMF-4 |

* 5 Fuses per pack, 10 packs per shelf carton.

Use with HLR in-line fuse holder page 13.