



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Ferrule style high speed fuse links

**FWP-32A14FI**

**UPC:**051712542906

### Dimensions:

- **Height:** 32 MM
- **Length:** 52 MM
- **Width:** 15 MM

**Weight:**.012 KG

### Warranties:

- Not Applicable

### Specifications:

- **Type:** FWP, Ferrule style
- **Application:** DC common bus, DC drives, power converters/rectifiers, reduced voltage starters
- **Amperage Rating:** 32A
- **Voltage Rating:** 700 Vac, 600 Vdc (UL)
- **Interrupt Rating:** 200kA ac RMS Symmetrical, 50kA at 300 Vdc
- **Fuse Indicator:** With Indicator
- **Packaging Type:** Standard
- **Used With:** Finger safe holders/blocks and striker
- **Pre Arc (I2T):** 68
- **Clearing (I2T):** Clearing at Rated voltage: 600
- **Diameter:** 14 MM
- **Material:** Ceramic
- **Color:** White
- **Class:** aR
- **Connection:** Ferrule end X ferrule end
- **Watt Losses:** 8W
- **Mounting:** Fuse holder and blocks
- **Quantity:** 10
- **Fuse Size:** 14 x 51 mm



**Supporting documents:** No Data

**Certifications:**

- CSA Certified
- UL Recognized

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.