

Data Tables

2 Loadcenters

TABLE 2-59. VALUE PACKS — SINGLE-PHASE — INDOOR — MAIN CIRCUIT BREAKER LOADCENTERS — COMBINATION COVER AND BREAKERS INCLUDED SINGLE-PHASE, 3-WIRE — 120/240 VAC — FACTORY BONDED SPLIT NEUTRAL — ALUMINUM BUS

| Main Breaker Type | Maximum Main Ampere Rating | Maximum Number 1-Inch (25.4 mm) | | Wire Size Range | Breakers Included | Loadcenter | |
|-------------------|----------------------------|---------------------------------|----------|---|--|---|--|
| | | Spaces | Circuits | | | Catalog Number | UPC Code |
| BR 10 kAIC | 100 | 20 | 20 | #6 – 1/0 | 5-BR120 & 1 BR230 6-BR120, 6-BR115, 1-BR230 & 1-BR250 | BR2020B100V BR2020B100V4 | 786676444255 782113491646 |
| | 150 | 30 | 30 | #1 – 300 kcmil | 10-BR120 & 1-BR230 | BR3030B150V2 | 782114894446 |
| BW 10 kAIC | 200 | 20 | 40 | — — | 5-BR120 & 1-BR230 5-BD2020 & 1-BR230 | BR2040B200V BR2040B200V3 | 786676445702 782114894453 |
| | | 30 | 40 | — — — | 5-BR120 & 1 BR230 10-BR120 & 1-BR230 6-BR120, 6-BR115, 1-BR230 & 1-BR250 | BR3040B200V BR3040B200V2 BR3040B200V4 | 786676001106 782114894460 782113491653 |
| | 40 | 40 | — — | 5-BR120 & 1 BR230 10-BR120 & 1-BR230 | BR4040B200V BR4040B200V2 | 786676446204 782114894484 | |

TABLE 2-60. VALUE PACKS — SINGLE-PHASE — INDOOR — MAIN CIRCUIT BREAKER LOADCENTERS — COMBINATION COVER AND BREAKERS INCLUDED — SINGLE-PHASE, 3-WIRE — 120/240 VAC — FACTORY BONDED SPLIT NEUTRAL — COPPER BUS

| Main Breaker Type | Maximum Main Ampere Rating | Maximum Number 1-Inch (25.4 mm) | | Wire Range Size | Breakers Included | Loadcenter | |
|-------------------|----------------------------|---------------------------------|----------|-----------------|--|----------------------------------|------------------------------|
| | | Spaces | Circuits | | | Catalog Number | UPC Code |
| BR 10 kAIC | 100 | 20 | 20 | #6 – 1/0 | 5-BR120 & 1-BR230 | BR2020BC100V | 782113491639 |
| | | 30 | 30 | | | BR3030BC100V | 782113491639 |
| BW 10 kAIC | 200 | 30 | 40 | #1 – 300 kcmil | 5-BR120, 1-BR230 & 2-BR120AF 5-BR120, 1-BR230 & 2-BR120AF | BR3040BC200VA BR4040BC200VA | 782116103690 782116103706 |
| | | 40 | 40 | | | BR3040BC200V2 BR3040BC200VA15 | 782116484379 782116123285 |
| BW 10 kAIC | 200 | 30 | 40 | #1 – 300 kcmil | 10-BR120, 1-BR230 5-BR120, 1-BR230 & 2-BR115AF | BR3040BC200V2 BR3040BC200VA15 | 782116484379 782116123285 |
| | | 40 | 40 | | | BR4040BC200VA15 BR4040BC200V2 | 782116123292 782116484386 |

TABLE 2-61. VALUE PACKS — SINGLE-PHASE — OUTDOOR — MAIN CIRCUIT BREAKER LOADCENTERS — BREAKERS INCLUDED — SINGLE-PHASE, 3-WIRE — 120/240 VAC — INSULATED/BONDABLE NEUTRAL — ALUMINUM BUS

| Main Breaker Type | Maximum Main Ampere Rating | Maximum Number 1-Inch (25.4 mm) | | Wire Range Size | Breakers Included | Loadcenter | |
|-------------------|----------------------------|---------------------------------|----------|-----------------|-------------------|----------------|--------------|
| | | Spaces | Circuits | | | Catalog Number | UPC Code |
| BR 10 kAIC | 100 | 20 | 24 | #6 – 1/0 | 5-BR120 & 1 BR230 | BR2024B100RV | 786676002219 |
| BW 10 kAIC | 200 | 30 | 40 | #1 – 300 kcmil | 5-BR120 & 1 BR230 | BR3040B200RV | 786676002226 |

TABLE 2-62. VALUE PACKS — SINGLE-PHASE — INDOOR — MAIN LUG LOADCENTERS — BREAKERS INCLUDED — SINGLE-PHASE, 3-WIRE — 120/240 VAC — INSULATED/BONDABLE NEUTRAL — ALUMINUM BUS

| Main Breaker Type | Maximum Main Ampere Rating | Maximum Number 1-Inch (25.4 mm) | | Wire Range Size | Breakers Included | Loadcenter | |
|-------------------|----------------------------|---------------------------------|----------|-----------------|--------------------|----------------|--------------|
| | | Spaces | Circuits | | | Catalog Number | UPC Code |
| BW 10 kAIC | 200 | 30 | 40 | #1 – 300 kcmil | 10-BR120 & 1-BR230 | BR3040L200V2 | 782114894477 |