

## 240 VAC HEAVY-DUTY, FUSIBLE, NON-FUSIBLE, DOUBLE THROW

### Specifications

- ✓ 30 – 800 amperes.
- ✓ Horsepower rated.
- ✓ Suitable for service entrance use with neutral or ground lug kit installed.
- ✓ Suitable for use as a manually operated switch per 2002 NEC Article 702.
- ✓ Fusible and non-fusible.
- ✓ UL listed File No. E5239.

TABLE 6-21. FUSIBLE

Ampere Rating Main and Standby	Fuse Class Provision	Maximum Horsepower Ratings with Time Delay Fuses							Catalog Number			
		1-Phase ac			3-Phase ac			dc 250 V	NEMA 1 Enclosure Indoor	UPC Code	NEMA 3R Enclosure Rainproof	UPC Code
		240 V	480 V	600 V	240 V	480 V	600 V					
2-Pole — 240 Vac — 250 Vdc												
200	H	15	—	—	—	—	—	40	DT224FGK	782113614007	DT224FRK	782113614014
3-Pole — 240 Vac — 250 Vdc												
30	H	3	—	—	7-1/2	—	—	5	DT321FGK	782113426280	DT321FRK	782113426297
60	H	10	—	—	15	—	—	10	DT322FGK	782113426303	DT322FRK	782113426310
100	H	15	—	—	30	—	—	20	DT323FGK	782113426327	DT323FRK	782113426334
200	H	15	—	—	60	—	—	40	DT324FGK	782113614021	DT324FRK	782113614038
400	H	—	—	—	125	—	—	50	DT325FGK	782113725758	DT325FRK	782114215821
600 <sup>①</sup>	T	—	—	—	50	—	—	50	DT326FGK	782113725765	DT326FRK	782114733639

① Only available for use with fast acting fuses. Standard hp rating is shown.

TABLE 6-22. NON-FUSIBLE

Ampere Rating Main and Standby	Fuse Class Provision	Maximum Horsepower Ratings						Catalog Number				
		1-Phase ac			3-Phase ac			dc 250 V	NEMA 1 Enclosure Indoor	UPC Code	NEMA 3R Enclosure Rainproof	UPC Code
		240 V	480 V	600 V	240 V	480 V	600 V					
Non-Fusible 2-Pole — 240 Vac — 250 Vdc												
30	3	—	—	—	—	—	5	DT221UGK	782113439990	④	—	
60	10	—	—	—	—	—	10	DT222UGK	782113440002	④	—	
100	20	—	—	—	—	—	20	DT223UGK	782113440019	④	—	
200	15	—	—	—	—	—	40	DT224UGK	782113613932	DT224URK	782113713380	
400	—	—	—	—	—	—	50	DT225UGK	782113738253	DT225URK	782113752280	
600	—	—	—	—	—	—	—	DT226UGK	782113738284	④	—	
Non-Fusible 3-Pole — 240 Vac — 250 Vdc												
30	3	—	—	10	—	—	5	DT321UGK	782113440026	④	—	
60	10	—	—	20	—	—	10	DT322UGK	782113440033	④	—	
100	20	—	—	40	—	—	20	DT323UGK	782113440040	DT323URK	782113757032	
200	15	—	—	60	—	—	40	DT324UGK	782113613963	DT324URK	782113638874	
400	—	—	—	125	—	—	50	DT325UGK	782113696423	DT325URK	782116153466	
600	—	—	—	125	—	—	50	DT326UGK	782113696454	④	—	
800	—	—	—	125	—	—	50	DT327UGK <sup>②③</sup>	782113696485	④	—	
800	—	—	—	125	—	—	50	DT327UGK-N	782114176900	④	—	

② **WARNING!** Switch is not approved for service entrance.

③ Field-installable neutral kit is not available. If a neutral is required, order the catalog number shown in the table with “N” suffix.

④ Contact the Safety Switch Flex Center (1-888-329-9272) for availability of this product.

