

Product Selection

2

Typical GHB



Type GHB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units ^①

Continuous Ampere Rating at 40°C	277/480 Vac Maximum, 125 Vdc Maximum ^②		277/480 Vac Maximum, 125/250 Vdc Maximum		277/480 Vac Maximum, 125/250 Vdc Maximum ^③	
	Single-Pole Catalog Number	Two-Pole Catalog Number	Single-Pole Catalog Number	Two-Pole Catalog Number	Single-Pole Catalog Number	Two-Pole Catalog Number
15	GHB1015 ^{④⑤}	GHB2015 ^④	GHB1015 ^{④⑤}	GHB2015 ^④	GHB3015 ^④	GHB2015 ^④
20	GHB1020 ^{④⑤}	GHB2020 ^④	GHB1020 ^{④⑤}	GHB2020 ^④	GHB3020 ^④	GHB2020 ^④
25	GHB1025	GHB2025	GHB1025	GHB2025	GHB3025	GHB2025
30	GHB1030	GHB2030	GHB1030	GHB2030	GHB3030	GHB2030
35	GHB1035	GHB2035	GHB1035	GHB2035	GHB3035	GHB2035
40	GHB1040	GHB2040	GHB1040	GHB2040	GHB3040	GHB2040
45	GHB1045	GHB2045	GHB1045	GHB2045	GHB3045	GHB2045
50	GHB1050	GHB2050	GHB1050	GHB2050	GHB3050	GHB2050
60	GHB1060	GHB2060	GHB1060	GHB2060	GHB3060	GHB2060
70	GHB1070	GHB2070	GHB1070	GHB2070	GHB3070	GHB2070
80	GHB1080	GHB2080	GHB1080	GHB2080	GHB3080	GHB2080
90	GHB1090	GHB2090	GHB1090	GHB2090	GHB3090	GHB2090
100	GHB1100	GHB2100	GHB1100	GHB2100	GHB3100	GHB2100

Type HGHB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40°C	277 Vac Maximum, 125 Vdc Maximum	
	Single-Pole Catalog Number	Two-Pole Catalog Number
15	HGHB1015 ^⑥	HGHB2015 ^⑥
20	HGHB1020 ^⑥	HGHB2020 ^⑥
25	HGHB1025	HGHB2025
30	HGHB1030	HGHB2030

Type GHQ Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40°C	277 Vac Maximum 14 kAIC, No DC Rating (HID and SWD)	
	Single-Pole Catalog Number	Two-Pole Catalog Number
15	GHQ1015 ^⑦	GHQ2015 ^⑦
20	GHQ1020 ^⑦	GHQ2020 ^⑦

Notes

- ① 480Y/277V, circuit breakers (Type GHB) not suitable for three-phase delta (480V).
- ② 15 through 70 ampere circuit breakers only.
- ③ Use two outside poles.
- ④ Uses 0.190 (4.83) –32 screw type clamp terminals.
- ⑤ Add suffix HID for High Intensity Discharge (HID) applications. 15 and 20 ampere, single-pole are SWD rated.
- ⑥ 15 and 20 ampere, single-pole are SWD rated.
- ⑦ Includes 4A33462H01 load clip.