


Catalog numbering system—Pow-R-Stock panelboard interiors



NEMA 1 Pow-R-Stock Panelboard Boxes

EZB 20 36 R BS

EZB are available boxes used for all Type 1 PRL1a, PRL2a, and PRL3a panels
Width in inches = 20 **Height in inches** = 36, 48, 60, or 72

R = Right-hand flange

NEMA 1 Pow-R-Stock Panelboard Trims

EZT 20 36 S

EZT are available laser cut trims used on all PRL1a, PRL2a, and PRL3a panels
Width in inches = 20 **Height in inches** = 36, 48, 60, or 72

Mounting

S = Surface
F = Flush

Main Breaker Kits

BK ED 100 T

Breaker kit
Breaker frame
ED or FD or KD
Trip rating 100, 125 150, 175, 200, 225, 250, 300, 350, 400

Mounting

T = Top
B = Bottom

Pow-R-Stock Plus program reference guide



Note: The colors shown in the table to the right correspond to the color-coding on the trim, interior and box product packaging labels. Be sure that all three parts match when delivering to your customer.

Unassembled panelboards—EZ Box™ and EZ Trim™

Ampere Rating	Maximum Number of Poles	Catalog Numbers					
		Interiors (Less Main Device)		Boxes	Trims (NEMA® 1)		NEMA 3R Enclosures
		Aluminum Bus	Copper Bus	NEMA 1	Surface	Flush	
Single-Phase, Three-Wire, 120/240V							
100	18	PRL1A1100X18A	PRL1A1100X18C	EZB2036R	EZT2036S	EZT2036F	GWPBQ2036PR
100	30	PRL1A1100X30A	PRL1A1100X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	30	PRL1A1225X30A	PRL1A1225X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	PRL1A1225X42AS	PRL1A1225X42CS	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	PRL1A1225X42A	PRL1A1225X42C	EZB2060R	EZT2060S	EZT2060F	GWPBQ2060PR
400	42	PRL1A1400X42A	PRL1A1400X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
Three-Phase, Four-Wire, 208Y/120V							
100	18	PRL1A3100X18A	PRL1A3100X18C	EZB2036R	EZT2036S	EZT2036F	GWPBQ2036PR
100	30	PRL1A3100X30A	PRL1A3100X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	30	PRL1A3225X30A	PRL1A3225X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	PRL1A3225L42AS	PRL1A3225L42CS	EZB2042R	EZT2042S	EZT2042F	GWPBQ2042PR
225	42	PRL1A3225X42AS	PRL1A3225X42CS	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	PRL1A3225X42A	PRL1A3225X42C	EZB2060R	EZT2060S	EZT2060F	GWPBQ2060PR
400	42	PRL1A3400X42A	PRL1A3400X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
Three-Phase, Four-Wire, 480Y/277V							
100	18	PRL2A3100X18A	PRL2A3100X18C	EZB2036R	EZT2036S	EZT2036F	GWPBQ2036PR
100	30	PRL2A3100X30A	PRL2A3100X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	30	PRL2A3225X30A	PRL2A3225X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	PRL2A3225L42AS	PRL2A3225L42CS	EZB2042R	EZT2042S	EZT2042F	GWPBQ2042PR
225	42	PRL2A3225X42AS	PRL2A3225X42CS	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	PRL2A3225X42A	PRL2A3225X42C	EZB2060R	EZT2060S	EZT2060F	GWPBQ2060PR
400	42	PRL2A3400X42A	PRL2A3400X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR

Summary of branch breakers available

Breaker	Poles	Ampere Rating	Voltage	kAIC Rating	Example	Panel Type
BAB	1	15–60	120V	10	BAB1020	PRL1A
	2	15–100	120/240V	10	BAB2020	PRL1A
	2	15–100	240V	10	BAB2040H	PRL1A
	3	15–100	240V	10	BAB3030H	PRL1A
QBGF	1	15–30	120V	10	QBGF1020	PRL1A
	2	15–40	120/240V	10	QBGF2040	PRL1A
QBHW	1	15–60	120V	22	QBHW1020	PRL1A
	2	15–100	120/240V	22	QBHW2020	PRL1A
	2	15–100	240V	22	QBHW2040H	PRL1A
	3	15–100	240V	22	QBHW3030H	PRL1A
GHQ	1	15–20	277V	14	GHQ1020	PRL2A
GHB	1	15–100	277V	14	GHB1020	PRL2A
	2	15–100	480Y/277V	14	GHB2040	PRL2A
	3	15–100	480Y/277V	14	GHB3060	PRL2A



Powering Business Worldwide