

Pow-R-Stock panelboards—EZ™ Boxes and EZ Trims

Ampere rating	Max. number of poles	Capability				Sub-feed breaker (225 A max.)	Catalog numbers			NEMA 3R enclosures	
		Main lugs	Main breaker	Through-feed lugs	Interiors (less main device)		Boxes		Trims (NEMA 1)		
							Aluminum bus	Copper bus	NEMA 1		Surface
Single-phase, three-wire 120/240 Vac											
100	18	■	■	■	N/A	PRL1A1100X18A	PRL1A1100X18C	EZB2036R	EZT2036S	EZT2036F	GWPBQ2036PR
100	30	■	■	■	100	PRL1A1100X30A	PRL1A1100X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
100	42	■	■	■	N/A	PRL1A1100X42A	PRL1A1100X42C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	30	■	■	■	100, 125, 150, 175, 200, 225	PRL1A1225X30A	PRL1A1225X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	■	■	N/A	N/A	PRL1A1225X42AS ①	PRL1A1225X42CS ①	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	■	■	■	100, 125, 150, 175, 200, 225	PRL1A1225X42A	PRL1A1225X42C	EZB2060R	EZT2060S	EZT2060F	GWPBQ2060PR
400	42	■	■	■	100, 125, 150, 175, 200, 225	PRL1A1400X42A	PRL1A1400X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
600	42	■	■	■	N/A		PRL1A1600X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
600	42	■	■	■	100, 125, 150, 175, 200, 225, 250, 300, 350, 400		PRL1A1600X42CL	EZB2090R	EZT2090S	EZT2090F	GWPBQ2090PR
Three-phase, four-wire 208Y/120 Vac											
100	18	■	■	■	N/A	PRL1A3100X18A	PRL1A3100X18C	EZB2036R	EZT2036S	EZT2036F	GWPBQ2036PR
100	30	■	■	■	100	PRL1A3100X30A	PRL1A3100X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
100	42	■	■	■	N/A	PRL1A3100X42A	PRL1A3100X42C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	30	■	■	■	100, 125, 150, 175, 200, 225	PRL1A3225X30A	PRL1A3225X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	■	N/A	N/A	N/A	PRL1A3225L42AS	PRL1A3225L42CS	EZB2042R	EZT2042S	EZT2042F	GWPBQ2042PR
225	42	■	■	N/A	N/A	PRL1A3225X42AS ①	PRL1A3225X42CS ①	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	■	■	■	100, 125, 150, 175, 200, 225	PRL1A3225X42A	PRL1A3225X42C	EZB2060R	EZT2060S	EZT2060F	GWPBQ2060PR
400	42	■	■	■	100, 125, 150, 175, 200, 225	PRL1A3400X42A	PRL1A3400X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
600	42	■	■	■	N/A		PRL1A3600X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
600	42	■	■	■	100, 125, 150, 175, 200, 225, 250, 300, 350, 400		PRL1A3600X42CL	EZB2090R	EZT2090S	EZT2090F	GWPBQ2090PR
Three-phase, four-wire 480Y/277 Vac											
100	18	■	■	■	N/A	PRL2A3100X18A	PRL2A3100X18C	EZB2036R	EZT2036S	EZT2036F	GWPBQ2036PR
100	30	■	■	■	100	PRL2A3100X30A	PRL2A3100X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
100	42	■	■	■	N/A	PRL2A3100X42A	PRL2A3100X42C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	30	■	■	■	100, 125, 150, 175, 200, 225	PRL2A3225X30A	PRL2A3225X30C	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	■	N/A	N/A	N/A	PRL2A3225L42AS	PRL2A3225L42CS	EZB2042R	EZT2042S	EZT2042F	GWPBQ2042PR
225	42	■	■	N/A	N/A	PRL2A3225X42AS ①	PRL2A3225X42CS ①	EZB2048R	EZT2048S	EZT2048F	GWPBQ2048PR
225	42	■	■	■	100, 125, 150, 175, 200, 225	PRL2A3225X42A	PRL2A3225X42C	EZB2060R	EZT2060S	EZT2060F	GWPBQ2060PR
400	42	■	■	■	100, 125, 150, 175, 200, 225	PRL2A3400X42A	PRL2A3400X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
600	42	■	■	■	N/A		PRL2A3600X42C	EZB2072R	EZT2072S	EZT2072F	GWPBQ2072PR
600	42	■	■	■	100, 125, 150, 175, 200, 225, 250, 300, 350, 400		PRL2A3600X42CL	EZB2090R	EZT2090S	EZT2090F	GWPBQ2090PR

① S = Short—no TFL or SFB provisions.

Note: The colors shown in the tables correspond to the color coding on the trim, interior and box product packaging labels. Be sure that all three parts match when delivering to your customer.

Note: Distributors can purchase boxes in quantities via the Distributor toolbox.