

CH Loadcenter Options and Accessories

CHSF2125



CHSF3125



CHFP



TDL



BINA



Field Installation and Parts

Description	Ordering Quantity ①	Catalog Number
Sub-feed lug blocks—two-pole, 125A, 3/4-inch (19.1 mm) spaces needed	1	CHSF2125
Sub-feed lug blocks—three-pole, 125A, 3/4-inch (19.1 mm) spaces needed	1	CHSF3125
Neutral/ground lug—add-on neutral or ground lug	1	NL20
	1	NL30
	1	NL300
Filler plates—3/4-inch (19.1 mm) space circuit breaker space	25	CHFP
CSR main circuit breaker filler plate (with hardware)	1	CSRFP
Door lock—12–42 circuits, and 100–225A	1	TDL
Sandlewood spray paint	1	SPCSW
ANSI-61 light gray touchup paint for outdoor loadcenters	1	SPC61
Isolated neutral assembly (computer circuits)	1	BINA
Circuit directory—adhesive backed	10	TCD
Cover screws	25	LCCS
Cover replacement latch 14-5/16 inch (363.55 mm) wide loadcenters only	1	CHRLS
Circuit marking strip (next to breakers)	10	CHMS
Circuit identification label (preprinted breaker labels next to breakers)	25	CHBL
Series rated caution label	25	SRL
Branch circuit numbering strip	20	CHNS
Bonding strap with screw	1	BSSUSE

Mechanical Interlock Covers

Covers mechanically interlock two breakers. Type A covers interlock two CH breakers mounted across from one another. Type B covers interlock a main Type CSR breaker with a Type CH.

Mechanical Interlocks

Type	Fits Loadcenter Catalog Numbers	Mechanical Interlock Panel Cover Catalog Number	
		Flush	Surface
CH8BRM Type A	CH12L125B, CH16L125B, CH12L3125B, CH14B100B	CH8BFM	CH8BSM
	CH20L125C, CH24L125C, CH18L3125C, CH24L3125C, CH22B100C, CH22N100C	CH8CFM	CH8CSM
	CH24L150D, CH32L150D, CH24L3225D, CH30L3150D	CH8DFM	CH8DSM
	CH42L225G, CH42L3225G	CH8GFM	CH8GSM
	Inner cover of Box B raintight	—	CH8BRM
	Inner cover of Box C raintight	—	CH8CRM
CH8EFM Type B	CH24B150E, CH24B200E	CH8EFM	CH8ESM
	CH32B150J, CH32B200J, CH324B200J, CH32N200J, CH32B225J	CH8JFM	CH8JSM
	CH42B200K, CH42N200K, CH42B225K	CH8KFM	CH8KSM
	CHPC32B150L, CHPC32B200L, CHPC32N200L	CHPC8B32LFM	—
	CHPC42B150L, CHPC42B200L, CHPC42N200L	CHPC8B42LFM	—
	CH8B150RF, CH8B200RF, CH8N200RF, CH24B150R, CH24B200R	CH3RDF7M	—
	CH32B150R, CH32B200R, CH32N200R, CH32B225R	CH3RDF9M	—
	CH42B200R, CH42N200R, CH42B225R	CH3RDF10M	—

Note

① Must be purchased in multiples of ordering quantities indicated.