

Atlantic City Electric/Delmarva Utility



200 Ampere Single-Position Meter Socket (UHIRS213BCVCH)



200 Ampere Single-Position Meter Socket



320 Ampere Lever Bypass Meter Socket (1009444CH)



200 Ampere Lever Bypass Meter Socket (UIH5213UCVCH)

Table 14. Atlantic City Electric/Delmarva Utility — Meter Socket Approval List

Cutler-Hammer Catalog Number	Description	Dimensions			Connections		Concentric Knockouts (See Page 11)				
		H	W	D	Line	Load	1	2	3	4	5
200 Ampere Single-Position — Residential Single-Phase											
UHIRS213BCVCH	200 A, 5 Terminal, SM Hub Open, OH ①②③	15.00	11.00	4.38	#8 – 350 kcmil	#8 – 350 kcmil	2.50	2.50	2.50	—	.50
UHIRS223ACVCH	200 A, 5 Terminal, SM Hub Cover Plate, UG ①②③	13.00	13.00	4.94	#8 – 350 kcmil	#8 – 350 kcmil	2.50	2.50	3.00	2.50	.50
200 Ampere Single-Position — Commercial w/ Lever Bypass											
UIH5213UCVCH	200 A, 5 Terminal, SM Hub Closure Plate OH/UG ①③④	19.00	13.00	4.94	#6 – 350 kcmil	#6 – 350 kcmil	3.00	2.50	3.00	3.00	.50
UIH7213UCVCH	200 A, 7 Terminal, LG Hub Closure Plate OH/UG ①③④	19.00	13.00	4.94	#6 – 350 kcmil	#6 – 350 kcmil	3.00	2.50	3.00	3.00	.50
320 Ampere Commercial — Residential Single-Phase w/ Lever Bypass											
1009444CH	320 A, 4 Terminal, LG Hub Cover Plate OH/UG ①③④	36.63	15.00	5.69	3/8-Inch Stud	3/8-Inch Stud	3.50	3.50	3.50	3.50	.50
100 Ampere Multi-Position Sockets — Residential Single-Phase											
Use 200 Ampere											
200 Ampere Multi-Position Sockets — Residential Single-Phase ⑤											
UHI2R2332TCVCH	200 A, 2 Position, LG Hub Open, OH, Ctr Fed ①②③	14.13	24.31	5.38	#6 – 350 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.50
UHI4R2352TCVCH	200 A, 4 Position, LG Hub Open, OH, Ctr Fed ①②③	14.13	40.63	5.38	1/0 – 500 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.75
UHI6R2392TTCVCH	200 A, 6 Position, LG Hub Open, OH, Ctr Fed ①②③	14.13	62.94	5.38	1/0 – 500 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.75
UHI2R2332ACVCH	200 A, 2 Position, Solid Top, UG, Ctr Fed ①②③	14.13	24.31	5.38	#6 – 350 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.50
UHI4R2352ACVCH	200 A, 4 Position, Solid Top, UG, Ctr Fed ①②③	14.13	40.63	5.38	1/0 – 500 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.75
UHI6R2392ACVCH	200 A, 5 Position, Solid Top, UG, Ctr Fed ①②③	14.13	62.94	5.38	1/0 – 500 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.75

- ① Ground connection.
- ② Horn bypass.
- ③ Inhibitor provided on jaws.
- ④ Lever bypass.
- ⑤ For 3 and 5 gang units, use 4 or 6 gang respectively.

Note: "100...CH" catalog numbers are specialty sockets for individual utilities and do not follow typical catalog numbering system.

Table 15. Cutler-Hammer Meter Socket Accessories

Cutler-Hammer Catalog Number	Description	Cutler-Hammer Catalog Number	Description
ARP00003CH1	1.00-Inch Hub	ARP00008CH	Small Hub Closure Plate — Aluminum
ARP00004CH12	1.25-Inch Hub	ARP00016CHB	Large Hub Closure Plate
ARP00005CH15	1.50-Inch Hub	ARP00015CHAP	Hub Adapter Plate — Large to Small
ARP00006CH2	2.00-Inch Hub — Small Opening	ARP00035CHJ	Replacement — Plug-in Fifth Terminal (R and RS Models Only)
ARP00007CH25	2.50-Inch Hub — Small Opening	ARP00039CH	Replacement Block Assembly for 100 A Sockets — 2/0 Maximum
ARP00017CH2	2.00-Inch Hub — Large Opening	ARP00048CH	Replacement Block Assembly for 200 A Sockets — 350 Maximum
ARP00018CH25	2.50-Inch Hub — Large Opening	ARP00354CH	Replacement Block Assembly for 150 A Sockets — 250 Maximum
ARP00019CH3	3.00-Inch Hub — Large Opening	ARP00129CH	#4 – 600 kcmil Lug
ARP00021CH4	4.00-Inch Hub — Large Opening	ARP00427CH	#6 – 350 kcmil Dual Lug
ARP00002CHB	Small Hub Closure Plate	ARP00119CH	#6 – 350 kcmil Lug