

Product Selection by Utility

Duke Power Utility



**100 Ampere Single-Position
Meter Socket (UTRS101BCH)**



**320 Ampere Lever Bypass
Meter Socket (UTH4330UCH)**



**200 Ampere Lever Bypass
Meter Socket (UTH7213UCH)**



**200 Ampere Multi-Position
Meter Socket (UT3R2332TCH)**

Table 4. Duke Power Utility — Meter Socket Distributor Net Price Sheet

Cutler-Hammer Catalog Number	Description	Dimensions			Connections		Concentric Knockouts (See Page 7)				
		H	W	D	Line	Load	1	2	3	4	5
100 – 125 Ampere Single-Position — Residential											
UTRS101BCH	125 A, 4 Terminal, SM Hub Open, OH/UG ①	10.88	8.00	3.50	#8 – 2/0	#8 – 2/0	1.50	1.50	2.00	1.25	—
200 Ampere Single-Position — Residential											
UTRS202BCH	200 A, 4 Terminal, SM Hub Open, OH ①	14.00	8.00	4.38	#8 – 250 kcmil	#8 – 250 kcmil	2.50	2.50	2.50	—	.50
UTRS213CCH	200 A, 4 Terminal, SM Hub Cover Plate, OH/UG ①	15.00	11.00	4.38	#8 – 350 kcmil	#8 – 350 kcmil	2.50	2.50	2.50	2.50	.50
UTRS223ACH	200 A, 4 Terminal, Solid Top, UG ①	13.00	13.00	5.00	#8 – 350 kcmil	#8 – 350 kcmil	2.50	2.50	3.00	2.50	.50
320 Ampere Commercial — Residential w/ Lever Bypass											
UTH4330UCH	320 A, 4 Terminal, LG Hub Cover Plate, OH/UG ①②	36.63	15.00	5.69	3/8" Stud	3/8" Stud	3.50	3.50	3.50	3.50	.50
UTH4338UCH	320 A, 4 Terminal, LG Hub Cover Plate, OH/UG ①②	36.63	15.00	5.69	Dual 250 kcmil	Dual 250 kcmil	3.50	3.50	3.50	3.50	.50
UTH4339UCH	320 A, 4 Terminal, LG Hub Cover Plate, OH/UG ①②	36.63	15.00	5.69	Dual 350 kcmil	Dual 350 kcmil	3.50	3.50	3.50	3.50	.50
200 Ampere Single-Position — Commercial w/ Lever Bypass											
UTH5213C or UCH	200 A, 5 Terminal, SM or LG Hub Cover Plate, OH/UG ①②	19.00	13.00	5.00	#6 – 350 kcmil	#6 – 350 kcmil	3.00	2.50	3.00	3.00	.50
UTH7213C or UCH	200 A, 7 Terminal, SM or LG Hub Cover Plate, OH/UG ①②	19.00	13.00	5.00	#6 – 350 kcmil	#6 – 350 kcmil	3.00	2.50	3.00	3.00	.50
320 Ampere Single-Position — Commercial w/ Lever Bypass											
1009181CH	320 A, 7 Terminal, LG Hub Closure Plate, OH ①④	34.50	15.00	5.69	⑤	⑤	3.50	3.50	3.50	3.50	.50
1008543CH	320 A, 7 Terminal, LG Hub Closure Plate, OH/UG ①④	39.88	20.00	6.50	⑤	⑤	4.00	4.00	4.00	4.00	.50
100 Ampere Multi-Position — Residential											
UT2R1121BCH	100 A, 2 Position, SM Hub Open, OH/UG, Center Feed ①	14.13	24.31	4.50	#6 – 250 kcmil	#8 – 2/0	2.50	2.50	2.50	2.50	.50
UT3R1121BCH	100 A, 3 Position, SM Hub Open, OH/UG, Center Feed ①	14.13	32.47	4.50	#6 – 250 kcmil	#8 – 2/0	2.50	2.50	2.50	2.50	.50
UT4R1121BCH	100 A, 4 Position, SM Hub Open, OH/UG, Center Feed ①	14.13	40.63	4.50	#6 – 250 kcmil	#8 – 2/0	2.50	2.50	2.50	2.50	.50
UT5R1121BCH	100 A, 5 Position, SM Hub Open, OH/UG, Center Feed ①	14.13	48.78	4.50	#6 – 250 kcmil	#8 – 2/0	2.50	2.50	2.50	2.50	.50
UT6R1131BCH	100 A, 6 Position, SM Hub Open, OH/UG, Center Feed ①	14.13	56.94	4.50	#6 – 350 kcmil	#8 – 2/0	2.50	2.50	2.50	2.50	.50
200 Ampere Multi-Position — Residential											
UT2R2332TCH	200 A, 2 Position, LG Hub Open, OH/UG, Center Feed ①	14.13	24.31	5.38	#6 – 350 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.50
UT3R2332TCH	200 A, 3 Position, LG Hub Open, OH/UG, Center Feed ①	14.13	32.47	5.38	#6 – 350 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.50
UT4R2352TCH	200 A, 4 Position, LG Hub Open, OH/UG, Center Feed ①	14.13	40.63	5.38	1/0 – 500 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.75
UT5R2392TTCH	200 A, 5 Position, LG Hub Open, OH/UG, Center Feed ①	14.13	54.78	5.38	1/0 – 500 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.75
UT6R2392TTCH	200 A, 6 Position, LG Hub Open, OH/UG, Center Feed ①	14.13	62.94	5.38	1/0 – 500 kcmil	#8 – 250 kcmil	2.50	2.50	3.00	2.50	.75

① Ground connection.

② Steel enclosure.

⑤ Single #600 kcmil/Dual #250 kcmil.

② Lever bypass.

④ Anti inversion clip installed.

Note: "100...CH" catalog numbers are specialty sockets for individual utilities and do not follow typical catalog numbering system.

Table 5. Cutler-Hammer Meter Socket Accessories

Cutler-Hammer Catalog Number	Description	Cutler-Hammer Catalog Number	Description
ARP00003CH1	1.00-Inch Hub	ARP00008CH	Small Hub Closure Plate — Aluminum
ARP00004CH12	1.25-Inch Hub	ARP00016CHB	Large Hub Closure Plate
ARP00005CH15	1.50-Inch Hub	ARP00015CHAP	Hub Adapter Plate — Large to Small
ARP00006CH2	2.00-Inch Hub — Small Opening	ARP00035CHJ	Replacement — Plug-in Fifth Terminal (R and RS Models Only)
ARP00007CH25	2.50-Inch Hub — Small Opening	ARP00039CH	Replacement Block Assembly for 100 A Sockets — 2/0 Maximum
ARP00017CH2	2.00-Inch Hub — Large Opening	ARP00048CH	Replacement Block Assembly for 200 A Sockets — 350 Maximum
ARP00018CH25	2.50-Inch Hub — Large Opening	ARP00354CH	Replacement Block Assembly for 150 A Sockets — 250 Maximum
ARP00019CH3	3.00-Inch Hub — Large Opening	ARP00129CH	#4 – 600 kcmil Lug
ARP00021CH4	4.00-Inch Hub — Large Opening	ARP00427CH	#6 – 350 kcmil Dual Lug
ARP00002CHB	Small Hub Closure Plate	ARP00119CH	#6 – 350 kcmil Lug