

## Three-Phase—Type DT-3 60 Hz NEMA TP-1 Energy-Efficient—Aluminum Windings

## 480 Delta Volts to 208Y/120 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg) ①	Weathershield	Style Number
	FCAN	FCBN							
15	2 at +2.5%	4 at -2.5%	DT-3	150	912B	280B	204 (93)	WS38	V48M28T15EE
30	2 at +2.5%	4 at -2.5%	DT-3	150	912B	280B	291 (132)	WS38	V48M28T30EE
37.5	2 at +2.5%	4 at -2.5%	DT-3	150	912B	280B	381 (173)	WS38	V48M28T37EE
45	2 at +2.5%	4 at -2.5%	DT-3	150	912B	280B	351 (159)	WS38	V48M28T45EE
50	2 at +2.5%	4 at -2.5%	DT-3	150	914D	280B	531 (241)	WS39	V48M28T50EE
75	2 at +2.5%	4 at -2.5%	DT-3	150	914D	280B	553 (251)	WS39	V48M28T75EE
112.5	2 at +2.5%	4 at -2.5%	DT-3	150	916A	280B	793 (360)	WS19	V48M28T12EE
150	2 at +2.5%	4 at -2.5%	DT-3	150	916A	280B	913 (415)	WS19	V48M28T49EE
225	2 at +2.5%	4 at -2.5%	DT-3	150	928	657B	1160 (527)	WS41	V48M28T22EE
300	2 at +2.5%	4 at -2.5%	DT-3	150	929	657B	1415 (642)	WS42	V48M28T33EE
500	2 at +2.5%	2 at -2.5%	DT-3	150	924	428B	2415 (1097)	WS40	V48D28T55EE
750	2 at +2.5%	4 at -2.5%	DT-3	150	920E	275A	3340 (1516)	WS35	V48M28T77EE
15	2 at +2.5%	4 at -2.5%	DT-3	115	912B	280B	202 (92)	WS38	V48M28F15EE
30	2 at +2.5%	4 at -2.5%	DT-3	115	912B	280B	311 (141)	WS38	V48M28F30EE
45	2 at +2.5%	4 at -2.5%	DT-3	115	912B	280B	418 (190)	WS38	V48M28F45EE
75	2 at +2.5%	4 at -2.5%	DT-3	115	914D	280B	581 (264)	WS39	V48M28F75EE
112.5	2 at +2.5%	4 at -2.5%	DT-3	115	916A	280B	829 (376)	WS19	V48M28F12EE
150	2 at +2.5%	4 at -2.5%	DT-3	115	916A	280B	996 (452)	WS19	V48M28F49EE
225	2 at +2.5%	4 at -2.5%	DT-3	115	918A	280B	1569 (712)	WS34	V48M28F22EE
300	2 at +2.5%	4 at -2.5%	DT-3	115	923	280B	1908 (866)	WS37	V48M28F33EE
500	2 at +2.5%	4 at -2.5%	DT-3	115	920E	275A	3117 (1415)	WS35	V48M28F55EE
15	2 at +2.5%	4 at -2.5%	DT-3	80	912B	280B	276 (125)	WS38	V48M28B15EE
30	2 at +2.5%	4 at -2.5%	DT-3	80	912B	280B	350 (159)	WS38	V48M28B30EE
45	2 at +2.5%	4 at -2.5%	DT-3	80	914D	280B	560 (254)	WS39	V48M28B45EE
75	2 at +2.5%	4 at -2.5%	DT-3	80	916A	280B	810 (368)	WS19	V48M28B75EE
112.5	2 at +2.5%	4 at -2.5%	DT-3	80	916A	280B	944 (429)	WS19	V48M28B12EE
150	2 at +2.5%	4 at -2.5%	DT-3	80	917	280B	1438 (653)	WS34	V48M28B49EE
225	2 at +2.5%	4 at -2.5%	DT-3	80	923	280B	1746 (793)	WS37	V48M28B22EE
300	2 at +2.5%	4 at -2.5%	DT-3	80	919E	275A	2400 (1090)	WS35	V48M28B33EE
500	2 at +2.5%	4 at -2.5%	DT-3	80	920E	275A	3418 (1552)	WS35	V48M28B55EE

**Notes**

① Weights subject to change.

Additional voltage combinations are available. Contact your local Eaton sales office for assistance if the voltage you require is not included in this catalog. For other ratings or styles not shown, or for special enclosure types (including stainless steel), refer to Eaton. Frame drawings/dimensions information begins on **Page V2-T2-213**.