

Three-Phase—Type DT-3 60 Hz NEMA TP-1 Energy-Efficient Electrostatically Shielded—Aluminum Windings

480 Delta Volts to 208Y/120 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg) ①	Weathershield	Style Number
	FCAN	FCBN							
15	2 at +2.5%	4 at -2.5%	DT-3	150	912B	283B	213 (97)	WS38	V48M28E15EE
30	2 at +2.5%	4 at -2.5%	DT-3	150	912B	283B	300 (136)	WS38	V48M28E30EE
37.5	2 at +2.5%	4 at -2.5%	DT-3	150	912B	283B	345 (157)	WS38	V48M28E37EE
45	2 at +2.5%	4 at -2.5%	DT-3	150	912B	283B	348 (158)	WS38	V48M28E45EE
50	2 at +2.5%	4 at -2.5%	DT-3	150	914D	283B	550 (250)	WS39	V48M28E50EE
75	2 at +2.5%	4 at -2.5%	DT-3	150	914D	283B	583 (265)	WS39	V48M28E75EE
112.5	2 at +2.5%	4 at -2.5%	DT-3	150	916A	283B	807 (366)	WS19	V48M28E12EE
150	2 at +2.5%	4 at -2.5%	DT-3	150	916A	283B	950 (431)	WS19	V48M28E49EE
225	2 at +2.5%	4 at -2.5%	DT-3	150	928	658B	1371 (622)	WS41	V48M28E22EE
300	2 at +2.5%	4 at -2.5%	DT-3	150	929	658B	1719 (780)	WS42	V48M28E33EE
500	2 at +2.5%	2 at -2.5%	DT-3	150	924	487A	2560 (1162)	WS40	V48D28E55EE
750	2 at +2.5%	4 at -2.5%	DT-3	150	920E	292A	3370 (1530)	WS35	V48M28E77EE
15	2 at +2.5%	4 at -2.5%	DT-3	115	912B	283B	204 (93)	WS38	V48M28F15EEES
30	2 at +2.5%	4 at -2.5%	DT-3	115	912B	283B	326 (148)	WS38	V48M28F30EEES
45	2 at +2.5%	4 at -2.5%	DT-3	115	912B	283B	419 (190)	WS38	V48M28F45EEES
75	2 at +2.5%	4 at -2.5%	DT-3	115	914D	283B	560 (254)	WS39	V48M28F75EEES
112.5	2 at +2.5%	4 at -2.5%	DT-3	115	916A	283B	805 (365)	WS19	V48M28F12EEES
150	2 at +2.5%	4 at -2.5%	DT-3	115	916A	283B	1012 (459)	WS19	V48M28F49EEES
225	2 at +2.5%	4 at -2.5%	DT-3	115	918A	283B	1589 (721)	WS34	V48M28F22EEES
300	2 at +2.5%	4 at -2.5%	DT-3	115	923	283B	1782 (809)	WS37	V48M28F33EEES
500	2 at +2.5%	4 at -2.5%	DT-3	115	920E	292A	3117 (1415)	WS35	V48M28F55EEES
15	2 at +2.5%	4 at -2.5%	DT-3	80	912B	283B	294 (133)	WS38	V48M28B15EEES
30	2 at +2.5%	4 at -2.5%	DT-3	80	912B	283B	374 (170)	WS38	V48M28B30EEES
45	2 at +2.5%	4 at -2.5%	DT-3	80	914D	283B	586 (266)	WS39	V48M28B45EEES
75	2 at +2.5%	4 at -2.5%	DT-3	80	916A	283B	807 (366)	WS19	V48M28B75EEES
112.5	2 at +2.5%	4 at -2.5%	DT-3	80	916A	283B	1005 (456)	WS19	V48M28B12EEES
150	2 at +2.5%	4 at -2.5%	DT-3	80	917	283B	1170 (531)	WS34	V48M28B49EEES
225	2 at +2.5%	4 at -2.5%	DT-3	80	923	283B	1764 (801)	WS37	V48M28B22EEES
300	2 at +2.5%	4 at -2.5%	DT-3	80	919E	292A	2317 (1052)	WS35	V48M28B33EEES
500	2 at +2.5%	4 at -2.5%	DT-3	80	920E	292A	3379 (1534)	WS35	V48M28B55EEES

Notes

① Weights subject to change.

For other ratings or styles not shown, or for special enclosure types (including stainless steel), refer to Eaton. Frame drawings/dimensions information begins on **Page V2-T2-213**.