



Powering Business Worldwide

pe.eaton.com

Series C, K-frame Molded Case Mining Circuit Breaker

E2K3400MGWU66

UPC:782114223581

Dimensions:

- **Height:** 10.13 IN
- **Length:** 4.1 IN
- **Width:** 5.5 IN

Weight:11.5 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Specialty complete
- **Amperage Rating:** 400A
- **Interrupt Rating:** 65 kAIC at 240V, 35 kAIC at 480V, 25 kAIC at 600V, 10 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 250 Vdc
- **Frame Size:** K-frame
- **Magnetic Trip Range:** 750-1500A
- **Maximum Voltage:** 600V
- **Series:** Series C
- **Trip Type:** Interchangeable thermal-magnetic
- **Undervoltage Release:** 120V mining left pigtail rear

Supporting documents:

- [Breaker service centers](#)
- [E2 Mining Series Sales Brochure](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - E2K3400MGWU66](#)

Certifications:



- CSA Certified
- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.