



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Assembled Limit Switch

E50AS3

UPC:782113307435

### Dimensions:

- **Height:** 2.56 IN
- **Length:** 4.22 IN
- **Width:** 1.54 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Assembly
- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Actuator:** Side push roller
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A continuous
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50

### Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50AS3](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data



